


Modular Connectors and Tools

Data/Network/Telecom



KOBICONN MODULAR JACKS WITH 4" WIRE LEADS

(Types marked with † have 50µ" gold plated contacts, all others have 6µ" gold plated contacts)

• All wire leads have stripped and tinned terminations

For quantities of 1,000 and up, call for quote.

MOUSER STOCK NO.	Fig.	USOC Type	Positions-Contacts	Western * Electric Type	Color	Price Each			
						1	10	100	500
154-7616C	A	Handset	4-4	616C	Gray				
154-7616D	B	Handset	4-4	616D	Gray				
† 154-UL616M	C	Handset	4-4	616M	Gray				
154-7616M	C	Handset	4-4	616M	Gray				
154-7616P	D	Handset	4-4	616P	Gray				
154-7616W	E	Handset	4-4	616W	Gray				
154-7623D4	F	RJ11	6-4	623D4	Gray				
154-7623D6	F	RJ12	6-6	623D6	Gray				
† 154-UL623K4	G	RJ11	6-4	623K4	Gray				
154-7623K4	G	RJ11	6-4	623K4	Gray				
† 154-UL623K6	G	RJ12	6-6	623K6	Gray				
154-7623K6	G	RJ12	6-6	623K6	Gray				
154-7623P4	H	RJ11	6-4	623P4	Gray				
154-7623P6	H	RJ12	6-6	623P6	Gray				
154-7652A4	I	RJ11	6-4	698A4	Gray				
154-7652A6	I	RJ12	6-6	698A6	Gray				
† 154-UL641D	J	RJ45	8-8	641D	Gray				
154-7641D	J	RJ45	8-8	641D	Gray				
154-7647	J	RJ45	8-8K	647	Gray				

KOBICONN MODULAR JACKS WITH PCB LEADS

(Types marked with † have 50µ" gold plated contacts, all others have 6µ" gold plated contacts)

• Glass filled nylon • PC Mount

For quantities of 1,000 and up, call for quote.

MOUSER STOCK NO.	Fig.	USOC Type	Positions-Contacts	Western * Electric Type	Color	Price Each			
						1	10	100	500
† 154-UL6442	L	Handset	4-4	616PCB	Black				
† 154-UL6443	M	Handset	4-4	616PCB	Black				
† 154-UL6641	N	RJ11	6-4	623PCB	Black				
† 154-UL6661	N	RJ12	6-6	623PCB	Black				
† 154-UL6642	K	RJ11	6-4	623PCB	Black				
† 154-UL6662	L	RJ12	6-6	623PCB	Black				
† 154-UL6643	M	RJ11	6-4	623PCB	Black				
† 154-UL6663	M	RJ12	6-6	623PCB	Black				
† 154-UL6881	K	RJ45	8-8	641PCB	Black				
† 154-UL6882	L	RJ45	8-8	641PCB	Black				
† 154-UL6883	M	RJ45	8-8	641PCB	Black				
† 154-7641PCB	O	RJ45	8-8	641PCB	Gray				

KOBICONN MODULAR PLUGS


(Types marked with † have 50µ" gold plated contacts, all others have 6µ" gold plated contacts)

* 616 Type - 4 conductor for handset to telephone use; 623 type - 4 or 6 conductor for telephone to wall use; 641 type - 8 conductor for telephone to wall or modern dialer use.

For quantities of 1,000 and up, call for quote.

MOUSER STOCK NO.	Fig.	USOC Type	Positions-Contacts	Western * Electric Type	Color	Price Each			
						1	10	100	500
† 154-UL6164	P	Handset	4-4	616	Clear				
154-7616	P	Handset	4-4	616	Clear				
† 154-UL6234	P	RJ11	6-4	623	Clear				
154-7623-4	P	RJ11	6-4	623	Clear				
† 154-UL6236	P	RJ12	6-6	623	Clear				
154-7623-6	P	RJ12	6-6	623	Clear				
† 154-UL6418	P	RJ45	8-8	641	Clear				
154-7641	P	RJ45	8-8	641	Clear				

MODULAR CRIMPING TOOLS



Crimping Tool

For quantities greater then listed, call for quote.

MOUSER STOCK NO.	Fig.	Type of Use	Price Each	
			1	5
382-8100	A	6P/4C and 4P/4C modular plugs		

Economy 3-Way Crimping Tools

- Cuts, strips, and crimps
- Black oxide finish
- Hardened steel frame
- Lightweight and durable

For quantities greater then listed, call for quote.

MOUSER STOCK NO.	Fig.	Type of Use	Price Each	
			1	5
382-2094C	B	For 4P 4C and 4P 2C plugs		