

HIROSE Modular Connectors



This product is RoHS compliant.



HIROSE ELECTRIC CO., LTD.

TM SERIES

Features:

- Conforming to FCC standards. The 6-conductor model conforming to RJ-11 standards, the 8-conductor model conforming to RJ-45 and ISO8877 standards.

Applications:

- Telephones, Fax machines, Wireless applications, Modems, Intercoms, Computers, Communication equipment, LAN equipment, Medical equipment, Hubs, ISDN terminals

PCB Modular Jacks

For quantities of 100 and up, call for quote.

MOUSER STOCK NO.	Hirose Part No.	Fig.	Positions/Contacts	Type	Dim. (mm)			Price Each		
					W	H	D	1	10	50
PC Board Mount - Gray										
798-TM5RF4450	TM5RF-44(50)	A	4/4	RJ-9	20.0	11.0	10.5			
798-TM5RJ34450	TM5RJ3-44(50)	B	4/4	RJ-9	12.8	14.0	14.0			
PC Board Mount with Tin Hold-Down Tab - Gray										
798-TM5RF14450	TM5RF1-44(50)	C	4/4	RJ-9	20.0	11.0	10.5			
Low Profile - PC Board Mount - Top Entry - White										
798-TM3RA4450	TM3RA-44(50)	D	4/4	RJ-9	12.9	18.3	15.0			
798-TM3RA6650	TM3RA-66(50)	D	6/6	RJ-11	14.9	18.3	15.0			
PC Board Mount - Straight Dip Type - Gray										
798-TM2RE060650	TM2RE-0606(50)	E	6/6	RJ-11	17.2	16.0	15.4			
PC Board Mount - Right Angle Dip Type - Gray										
798-TM2REA060450	TM2REA-0604(50)	F	6/4	RJ-11	18.0	16.0	15.4			
PC Board Mount - Gray										
798-TM5RJ16450	TM5RJ1-64(50)	G	6/4	RJ-11	14.8	14.0	14.0			
798-TM5RJ16650	TM5RJ1-66(50)	G	6/6	RJ-11	14.8	14.0	14.0			
798-TM5RJ26450	TM5RJ2-64(50)	H	6/4	RJ-11	14.8	14.0	14.0			
798-TM5RJ26650	TM5RJ2-66(50)	H	6/6	RJ-11	14.8	14.0	14.0			
798-TM5RC6450	TM5RC-64(50)	I	6/4	RJ-11	18.0	21.1	14.3			
798-TM5RC6650	TM5RC-66(50)	I	6/6	RJ-11	18.0	21.1	14.3			
798-TM5RJ18850	TM5RJ1-88(50)	G	8/8	RJ-45	19.2	14.0	16.0			
798-TM5RJ2-8850	TM5RJ2-88(50)	H	8/8	RJ-45	18.6	14.0	14.0			
798-TM5RC-8850	TM5RC-88(50)	J	8/8	RJ-45	18.1	21.2	17.5			
Low Profile - PC Board Mount - Top Entry - White										
798-TM3RA8850	TM3RA-88(50)	K	8/8	RJ-45	16.9	18.3	15.0			
Right Angle - SMT - Female										
798-TM18RTO8850	TM18R-TO-88(50)	L	8/8	RJ-45	15.6	12.3	14.5			
PC Board Mount - Right Angle - With Ferrite Core - Gray										
798-TM5RL-8850	TM5RL-88(50)	M	8/8	RJ-45	14.0	11.7	17.0			
EMI Protection - Right Angle - Thru Hole - Female										
798-TM11R-5C-8850	TM11R-5C-88(50)	N	8/8	RJ-45	14.6	15.1	17.6			
Separate Ground Spring - EMI Shield - Right Angle - SMT										
798-TM24RSG-5A-88	TM24RSG-5A-88	O	8/8	RJ-45	15.0	14.5	13.0			
CAT6 - Right Angle - SMT - Black										
798-TM23R5A8850	TM23R-5A-88(50)	P	8/8	RJ-45	15.0	14.5	13.0			
Adaptor - Receptacle-to-Receptacle										
798-TM5RL88JJ50	TM5RL-88-JJ(50)	Q	8/8	RJ-45	18.6	17.0	37.5			

Ganged Jacks

For quantities of 100 and up, call for quote.

MOUSER STOCK NO.	Hirose Part No.	Fig.	Positions/Contacts	Type	Dim. (mm)			Price Each		
					W	H	D	1	10	50
PC Board Mount - Straight Dip Type - Gray										
798-TM2RE120850	TM2RE-1208(50)	R	2 x 6/4	RJ-11	28.2	16.0	15.4			
PC Board Mount - Right Angle Dip Type - Gray										
798-TM2REA120450	TM2REA-1204(50)	S	2 x 6/2	RJ-11	28.2	16.0	15.4			
798-TM2REA120850	TM2REA-1208(50)	S	2 x 6/4	RJ-11	28.2	16.0	15.4			
798-TM2REA-181850	TM2REA-1818(50)	S	3 x 6/6	RJ-11	39.2	16.0	15.4			
798-TM2REA-240850	TM2REA-2408(50)	S	4 x 6/2	RJ-11	50.2	16.0	15.4			
798-TM2REA241650	TM2REA-2416(50)	S	4 x 6/4	RJ-11	50.2	16.0	15.4			
798-TM2REA242450	TM2REA-2424(50)	S	4 x 6/6	RJ-11	50.2	16.0	15.4			
PC Board Mount - Side Entry - Gray										
798-TM5RJ1484850	TM5RJ1-4848(50)	S	8 x 6/6	RJ-11	93.0	14.0	14.0			
PC Board Mount - Low Profile - With Ferrite Core - Gray										
798-TM5RL323250	TM5RL-3232(50)	T	4 x 8/8	RJ-45	56.0	11.7	17.0			

Plugs


For quantities of 100 and up, call for quote.

MOUSER STOCK NO.	Hirose Part No.	Fig.	Positions/Contacts	Type	Dim. (mm)			Price Each		
					W	H	D	1	10	50
IDC Termination with Flat Line Cord										
798-TM3P-44P	TM3P-44P	U	4/4	----	7.7	6.6	13.4			
798-TM3P-64P	TM3P-64P	U	6/4	RJ-11	9.7	6.6	13.4			
798-TM3P66P	TM3P-66P	U	6/6	RJ-11	9.7	6.6	13.4			
798-TM8P-88P	TM8P-88P	U	8/8	RJ-45	11.7	6.6	22.5			

Boots

For quantities of 100 and up, call for quote.

MOUSER STOCK NO.	Hirose Part No.	Fig.	Positions/Contacts	Type	Color	Price Each		
						1	10	50
Boot for CAT6 Plug								
798-TM23P8BT01	TM23P-8-BT(01)	V	8	RJ-45	Black			



NEW AT MOUSER

DataNetworkTelecom

NEW AT MOUSER