

PHOENIX CONTACT M12 / M8 Cordsets





M12 / M8 THREADED CORD SETS

- Features:**
- Cable Jacket: (PUR) Polyurethane
 - Cable Color: Black
 - Connector Housing Color: Green
 - Connector Interface: Threaded Metal

- Specifications:**
- Current Rating: 4A
 - Temperature Range: -30° to 80°
 - IP-Degree: IP67 (IEC 60529)
 - Voltage Rating: 320V

For quantities of 100 and up, call for quote.

MOUSER STOCK NO.		Fig.	Phoenix Contact Type	No. of Con.	End 1	End 2	Length (m)	Price Each		
Mfr.	Mfr. Part No.							1	10	25
M8 Single-Ended Cord Sets - Straight Male Connector										
651	1681664	A	SAC-3P-M 8MS/1.5-PUR	3	Straight Male	Open	1.5			
651	1681677	A	SAC-3P-M 8MS/3.0-PUR	3	Straight Male	Open	3			
651	1681680	A	SAC-3P-M 8MS/5.0-PUR	3	Straight Male	Open	5			
M8 Single-Ended Cord Sets - Right Angle Male Connector										
651	1681693	B	SAC-3P-M 8MR/1.5-PUR	3	R/A Male	Open	1.5			
651	1681703	B	SAC-3P-M 8MR/3.0-PUR	3	R/A Male	Open	3			
651	1681716	B	SAC-3P-M 8MR/5.0-PUR	3	R/A Male	Open	5			
M8 Single-Ended Cord Sets - Straight Female Connector										
651	1669712	C	SAC-3P- 1.5-PUR/M 8FS	3	Straight Female	Open	1.5			
651	1669725	C	SAC-3P- 3.0-PUR/M 8FS	3	Straight Female	Open	3			
651	1669628	C	SAC-3P- 5.0-PUR/M 8FS	3	Straight Female	Open	5			
M8 Single-Ended Cord Sets - Right Angle Female Connector										
651	1669738	D	SAC-3P- 1.5-PUR/M 8FR	3	R/A Female	Open	1.5			
651	1669741	D	SAC-3P- 3.0-PUR/M 8FR	3	R/A Female	Open	3			
651	1669631	D	SAC-3P- 5.0-PUR/M 8FR	3	R/A Female	Open	5			
M12 Single-Ended Cord Sets - Straight Male Connector										
651	1668043	A	SAC-4P-M12MS/1.5-PUR	4	Straight Male	Open	1.5			
651	1668056	A	SAC-4P-M12MS/3.0-PUR	4	Straight Male	Open	3			
651	1668069	A	SAC-4P-M12MS/5.0-PUR	4	Straight Male	Open	5			
651	1682993	A	SAC-4P-M12MS/10.0-PUR	4	Straight Male	Open	10			
M12 Single-Ended Cord Sets - Right Angle Male Connector										
651	1668166	B	SAC-4P-M12MR/1.5-PUR	4	R/A Male	Open	1.5			
651	1668179	B	SAC-4P-M12MR/3.0-PUR	4	R/A Male	Open	3			
651	1668182	B	SAC-4P-M12MR/5.0-PUR	4	R/A Male	Open	5			
651	1694457	B	SAC-4P-M12MR/10.0-PUR	4	R/A Male	Open	10			
M12 Single-Ended Cord Sets - Straight Female Connector										
651	1668108	C	SAC-4P-1.5-PUR/M12FS	4	Straight Female	Open	1.5			
651	1668111	C	SAC-4P- 3.0-PUR/M12FS	4	Straight Female	Open	3			
651	1668124	C	SAC-4P- 5.0-PUR/M12FS	4	Straight Female	Open	5			
651	1683002	C	SAC-4P-10.0-PUR/M12FS	4	Straight Female	Open	10			
M12 Single-Ended Cord Sets - Right Angle Female Connector										
651	1668221	D	SAC-4P-1.5-PUR/M12FR	4	R/A Female	Open	1.5			
651	1668234	D	SAC-4P- 3.0-PUR/M12FR	4	R/A Female	Open	3			
651	1668247	D	SAC-4P- 5.0-PUR/M12FR	4	R/A Female	Open	5			
651	1681389	D	SAC-4P-10.0-PUR/M12FR	4	R/A Female	Open	10			
M12 Double-Ended Cord Sets - Straight Male / Straight Female Connectors										
651	1668357	E	SAC-4P-M12MS/0.3-PUR/M12FS	4	Straight Male	Straight Female	0.3			
651	1668360	E	SAC-4P-M12MS/0.6-PUR/M12FS	4	Straight Male	Straight Female	0.6			
651	1668373	E	SAC-4P-M12MS/1.5-PUR/M12FS	4	Straight Male	Straight Female	1.5			
651	1668386	E	SAC-4P-M12MS/3.0-PUR/M12FS	4	Straight Male	Straight Female	3			



Circular Connectors Phoenix Contact

M12 SPEEDCON CORD SETS

- Features:**
- Simple 1/2 turn connection
 - Compatible with all M12 standard threading
 - 90% time savings over standard M12
 - No special adapters required

- Specifications:**
- Current Rating: 4A
 - Temperature Range: -25° to 90° C
 - IP-Degree: IP65 & IP67
 - Voltage Rating: 300V/125V(5 pos)

For quantities of 100 and up, call for quote.

MOUSER STOCK NO.		Fig.	Phoenix Contact Type	No. of Con.	End 1	End 2	Length (m)	Price Each		
Mfr.	Mfr. Part No.							1	10	25
Single Ended Cord Sets-Straight										
651	1518643	A	SAC-3P-MS/ 1.5-PUR SCO	3	Straight Male	Open	1.5			
651	1518656	A	SAC-3P-MS/ 3.0-PUR SCO	3	Straight Male	Open	3			
651	1518669	A	SAC-3P-MS/ 5.0-PUR SCO	3	Straight Male	Open	5			
651	1518805	A	SAC-4P-MS/ 1.5-PUR SCO	4	Straight Male	Open	1.5			
651	1518818	A	SAC-4P-MS/ 3.0-PUR SCO	4	Straight Male	Open	3			
651	1518960	A	SAC-5P-MS/ 1.5-PUR SCO	5	Straight Male	Open	1.5			
651	1518973	A	SAC-5P-MS/ 3.0-PUR SCO	5	Straight Male	Open	3			
Single Ended Cord Sets-Right Angle										
651	1518685	B	SAC-3P-MR/1.5-PUR SCO	3	R/A Male	Open	1.5			
651	1518698	B	SAC-3P-MR/ 3.0-PUR SCO	3	R/A Male	Open	3			
651	1518847	B	SAC-4P-MR/ 1.5-PUR SCO	4	R/A Male	Open	1.5			
651	1518850	B	SAC-4P-MR/ 3.0-PUR SCO	4	R/A Male	Open	3			
651	1519008	B	SAC-5P-MR/ 1.5-PUR SCO	5	R/A Male	Open	1.5			
Double Ended Cord Sets-Straight										
651	1518740	C	SAC-3P-MS/ 1.5-PUR/FS SCO	3	Straight Male	Straight Female	1.5			
651	1518753	C	SAC-3P-MS/ 3.0-PUR/FS SCO	3	Straight Male	Straight Female	3			
651	1518902	C	SAC-4P-MS/ 1.5-PUR/FS SCO	4	Straight Male	Straight Female	1.5			
651	1518915	C	SAC-4P-MS/ 3.0-PUR/FS SCO	4	Straight Male	Straight Female	3			
651	1519066	C	SAC-5P-MS/ 1.5-PUR/FS SCO	5	Straight Male	Straight Female	1.5			
651	1519079	C	SAC-5P-MS/ 3.0-PUR/FS SCO	5	Straight Male	Straight Female	3			
Double Ended Cord Sets-Right Angle / Straight										
651	1518782	D	SAC-3P-MR/ 1.5-PUR/FS SCO	3	Straight Male	Straight Female	1.5			
651	1518795	D	SAC-3P-MR/ 3.0-PUR/FS SCO	3	Straight Male	Straight Female	3			
Y Cables										
651	1524200	E	SAC-3P-Y/2X 1.5-PUR SCO	2 x 3	Straight Male	Open	1.5			
651	1524213	E	SAC-3P-Y/2X-3.0-PUR SCO	2 x 3	Straight Male	Open	3			

