


HIROSE Wire-to-Board Connectors

RoHS Compliant This product is RoHS compliant.



DF1B SERIES - 2.5MM PITCH

Sockets For quantities of 200 and up, call for quote.

MOUSER STOCK NO.	Hirose Part No.	Fig.	No. of Contacts	Dimensions (mm)		Price Each		
				A	B	1	25	100
Single Row - Crimping								
798-DF1B-2S-2.5R	DF1B-2S-2.5R	A	2	5.0	2.5			
Single Row In-Line - Crimping - Full Lock								
798-DF1B-3ES-2.5RC	DF1B-3ES-2.5RC	B	3	5.0	9.0			
798-DF1B-4ES-2.5RC	DF1B-4ES-2.5RC	B	4	7.5	11.5			
Double Row - Crimping								
798-DF1B-4DS-2.5RC	DF1B-4DS-2.5RC	C	4	7.5	2.5			
798-DF1B-6DS-2.5RC	DF1B-6DS-2.5RC	C	6	10.0	5.0			
798-DF1B-10DS-2.5RC	DF1B-10DS-2.5RC	C	10	15.0	10.0			
798-DF1B-12DS-2.5RC	DF1B-12DS-2.5RC	C	12	17.5	12.5			
798-DF1B-16DS-2.5RC	DF1B-16DS-2.5RC	C	16	22.5	17.5			

Crimp Contacts


For quantities of 200 and up, call for quote.

MOUSER STOCK NO.	Hirose Part No.	Fig.	Plating	AWG	Price Each		
					1	25	100
ID Contact for Sockets							
798-DF1B-R24	DF1B-R24	--	Tin	24			
798-DF1B-R28	DF1B-R28	--	Tin	28			
798-DF1B-R26A06	DF1B-R26A(06)	--	Gold	26			
Crimping Contact for Sockets							
798-DF1B-2022SC	DF1B-2022SC	--	Tin	22			
798-DF1B-2428SC	DF1B-2428SC	--	Tin	24-28			
798-DF1B-2428SCA	DF1B-2428SCA	--	Gold	24-28			
ID Contact for Plugs							
798-DF1B-24PR	DF1B-24PR	--	Tin	24			
Crimping Contact for Plugs							
798-DF1B-2022PC	DF1B-2022PC	--	Tin	20-22			
798-DF1B-2428PC	DF1B-2428PC	--	Tin	24-28			
798-DF1B-2022PCB	DF1B-2022PCB	--	Gold	20-22			

Crimp Contacts (Reels)

For quantities of 200 and up, call for quote.

MOUSER STOCK NO.	Hirose Part No.	Fig.	Plating	AWG	Reel Qty.	Price Each
798-DF1B-2428PCF	DF1B-2428PCF	--	Tin	24-28	10000	



DF1E SERIES - 2.5MM PITCH FOR FULL LOCK

Sockets For quantities of 200 and up, call for quote.

MOUSER STOCK NO.	Hirose Part No.	Fig.	No. of Contacts	Dimensions (mm)		Price Each		
				A	B	1	25	100
Single Row - Crimping								
798-DF1E-2S-2.5C	DF1E-2S-2.5C	A	2	2.5	8.0			
798-DF1E-3S-2.5C	DF1E-3S-2.5C	A	3	5.0	10.5			
798-DF1E-4S-2.5C	DF1E-4S-2.5C	A	4	7.5	13.0			
798-DF1E-5S-2.5C	DF1E-5S-2.5C	A	5	10.0	15.5			
798-DF1E-6S-2.5C	DF1E-6S-2.5C	A	6	12.5	18.0			
Retainer								
798-DF1E-2RS/P-2.5	DF1E-2RS/P-2.5	B	2	8.0	2.5			
798-DF1E-3RS/P-2.5	DF1E-3RS/P-2.5	B	3	10.5	5.0			
798-DF1E-6RS/P-2.5	DF1E-6RS/P-2.5	B	6	18.0	12.5			

Crimp Contacts

For quantities of 200 and up, call for quote.

MOUSER STOCK NO.	Hirose Part No.	Fig.	No. of Contacts	AWG	Price Each		
					1	25	100
Crimping Contact for Plugs							
798-DF1E-2022PC	DF1E-2022PC	--	Tin	20-22			
798-DF1E-2428PC	DF1E-2428PC	--	Tin	24-28			

Headers

For quantities of 200 and up, call for quote.

MOUSER STOCK NO.	Hirose Part No.	Fig.	No. of Contacts	Dimensions (mm)		Price Each		
				A	B	1	25	100
Single Row - Straight - Tin - Thru-Hole								
798-DF1BZ-4P-2.5DSA	DF1BZ-4P-2.5DSA	D	4	7.5	12.5			
798-DF1BZ-6P-2.5DSA	DF1BZ-6P-2.5DSA	D	6	12.5	17.5			
798-DF1BZ-10P-2.5DSA	DF1BZ-10P-2.5DSA	D	10	22.5	27.5			
Single Row - Straight - Gold - Thru-Hole								
798-DF1B-2P-2.5DSA01	DF1B-2P-2.5DSA(01)	D	2	2.5	7.5			
798-DF1B-6P-2.5DSA01	DF1B-6P-2.5DSA(01)	D	6	12.5	17.5			
Single Row - Right Angle - Tin - Thru-Hole								
798-DF1BZ-3P-2.5DS	DF1BZ-3P-2.5DS	E	3	5.0	10.0			
798-DF1BZ-4P-2.5DS	DF1BZ-4P-2.5DS	E	4	7.5	12.5			
798-DF1BZ-6P-2.5DS	DF1BZ-6P-2.5DS	E	6	12.5	17.5			
Single Row - Right Angle - Gold - Thru-Hole								
798-DF1B-2P-2.5DS01	DF1B-2P-2.5DS(01)	E	2	2.5	7.5			
798-DF1B-4P-2.5DS01	DF1B-4P-2.5DS(01)	E	4	7.5	12.5			
Double Row - Straight - Tin - Thru-Hole								
798-DF1BZ-8DP-2.5DSA	DF1BZ-8DP-2.5DSA	F	8	7.5	12.5			
798-DF1BZ-10DP-2.5DSA	DF1BZ-10DP-2.5DSA	F	10	10.0	15.0			
798-DF1BZ-16DP-2.5DSA	DF1BZ-16DP-2.5DSA	F	16	17.5	22.5			
798-DF1BZ-26DP-2.5DSA	DF1BZ-26DP-2.5DSA	F	26	30.0	35.0			
798-DF1BZ-40DP-2.5DSA	DF1BZ-40DP-2.5DSA	F	40	47.5	52.5			
Double Row - Straight - Gold - Thru-Hole								
798-DF1B14DP-2.5DSA01	DF1B-14DP-2.5DSA(01)	F	14	15.0	20.0			
798-DF1B16DP-2.5DSA01	DF1B-16DP-2.5DSA(01)	F	16	17.5	22.5			
798-DF1B20DP-2.5DSA01	DF1B-20DP-2.5DSA(01)	F	20	22.5	27.5			
Double Row - Right Angle - Tin - Thru-Hole								
798-DF1BZ-4DP-2.5DS	DF1BZ-4DP-2.5DS	G	4	7.5	2.5			
798-DF1BZ-6DP-2.5DS	DF1BZ-6DP-2.5DS	G	6	10.0	5.0			
798-DF1BZ-8DP-2.5DS	DF1BZ-8DP-2.5DS	G	8	12.5	7.5			
798-DF1BZ-10DP-2.5DS	DF1BZ-10DP-2.5DS	G	10	15.0	10.0			
798-DF1BZ-14DP-2.5DS	DF1BZ-14DP-2.5DS	G	14	20.0	15.0			
Double Row - Right Angle - Gold - Thru-Hole								
798-DF1B-6DP-2.5DS01	DF1B-6DP-2.5DS(01)	G	6	20.0	5.0			
798-DF1B-20DP-2.5DS01	DF1B-20DP-2.5DS(01)	G	20	27.5	22.5			

Plugs

For quantities of 200 and up, call for quote.

Single Row In-Line - Crimping - Full Lock								
798-DF1B-2EP-2.5RC	DF1B-2EP-2.5RC	H	2	2.5	8.9			
798-DF1BA-4EP-2.5RC	DF1BA-4EP-2.5RC	H	4	7.5	12.1			
Double Row - Straight - Crimping - Simple Lock								
798-DF1BA-6DEP-2.5RC	DF1BA-6DEP-2.5RC	I	6	5.0	11.0			
798-DF1BA-14DEP-2.5RC	DF1BA-14DEP-2.5RC	I	14	15.0	21.1			
Double Row - Straight - Crimping - Full Lock								
798-DF1B-10DEP-2.5RC	DF1B-10DEP-2.5RC	J	10	10.0	15.0			

NEW FROM HIROSE

Rectangular Connectors

Hirose

NEW FROM HIROSE