


HONEYWELL Toggle Switches


Honeywell

Sensing and Control

 This product is RoHS compliant.

MICRO SWITCH™ TOGGLE SWITCHES

MOUSER STOCK NO.	Honeywell Part No.	Fig.	Contact Form	Circuitry	Action	Termination	Lever Type	Price Each		
								1	10	50
785-11TS115-3	11TS115-3	A	SPDT	ON-ON	2 position	Solder	Standard			
785-11TS15-1	11TS15-1	A	SPDT	ON-OFF-ON	3 position	Screw	Standard			
785-11TS15-2	11TS15-2	A	SPDT	OFF-ON	2 position	Screw	Standard			
785-11TS15-5	11TS15-5	A	SPDT	(ON)-OFF-ON	3 position	Screw	Standard			
785-11TS15-6	11TS15-6	A	SPDT	(ON)-OFF	2 position	Screw	Standard			
785-11TS15-7	11TS15-7	A	SPDT	(ON)-OFF-(ON)	3 position	Screw	Standard			
785-11TS95-2	11TS95-2	A	SPDT	ON-OFF-ON	2 position	Quick Connect	Standard			
785-11TS95-7	11TS95-7	A	SPDT	(ON)-OFF-(ON)	3 position	Quick Connect	Standard			
785-11TW1-1	11TW1-1	B	SPDT	(ON)-OFF-(ON)	3 position	Quick Connect	Standard			
785-11TW1-3	11TW1-3	B	SPDT	ON-ON	2 position	Solder	Standard			
785-11TW8-3G	11TW8-3G	B	SPDT	ON-ON	2 position	Solder	Locking			
785-12TW1-3	12TW1-3	B	DPDT	ON-ON	2 position	PCB	Standard			
785-12TW1-5	12TW1-5	B	DPDT	(ON)-OFF-ON	3 position	Solder	Standard			
785-12TW1-7	12TW1-7	B	DPDT	(ON)-OFF-(ON)	3 position	Solder	Standard			
785-12TS115-1	12TS115-1	C	DPDT	ON-OFF-ON	3 position	Solder	Standard			
785-12TS115-2	12TS115-2	C	DPST	OFF-ON	2 position	Solder	Standard			
785-12TS115-3	12TS115-3	C	DPDT	ON-ON	2 position	Solder	Standard			
785-12TS15-1	12TS15-1	C	DPDT	ON-OFF-ON	3 position	Screw	Standard			
785-12TS15-2	12TS15-2	C	DPST	OFF-ON	2 position	Screw	Standard			
785-12TS15-3	12TS15-3	C	DPDT	ON-ON	2 position	Screw	Standard			
785-12TS15-6	12TS15-6	C	DPST	(ON)-OFF	2 position	Screw	Standard			
785-12TS15-7	12TS15-7	C	DPDT	(ON)-OFF-(ON)	3 position	Screw	Standard			
785-12TS95-3	12TS95-3	C	DPDT	ON-ON	2 position	Quick Connect	Standard			
785-12TS95-70	12TS95-70	C	DPDT	(ON)-OFF-(ON)	3 position	Quick Connect	Standard			
785-12TW8-7E	12TW8-7E	D	DPDT	(ON)-OFF-(ON)	3 position	Solder	Locking			
785-1NT1-2	1NT1-2	E	SPST	OFF-ON	2 position	Screw	Standard			
785-1NT1-3	1NT1-3	E	SPDT	ON-ON	2 position	Screw	Standard			
785-1NT1-6	1NT1-6	E	SPST	(ON)-OFF	2 position	Screw	Standard			
785-1NT1-7	1NT1-7	E	SPDT	(ON)-OFF-(ON)	3 position	Screw	Standard			
785-1NT1-8	1NT1-8	E	SPDT	ON-ON	2 position	Screw	Standard			
785-1NT1-3D	1NT1-3D	F	SPDT	ON-ON	2 position	Screw	Locking			
785-1TL1-1	1TL1-1	F	SPDT	ON-OFF-ON	3 position	Screw	Standard			
785-1TL1-1A	1TL1-1A	F	SPDT	ON-OFF-ON	3 position	Screw	Locking			
785-1TL1-2	1TL1-2	F	SPST	OFF-ON	2 position	Screw	Standard			
785-1TL1-2D	1TL1-2D	F	SPST	OFF-ON	2 position	Screw	Locking			
785-1TL1-3	1TL1-3	F	SPDT	OFF-ON	2 position	Screw	Standard			
785-1TL1-3D	1TL1-3D	F	SPDT	ON-ON	2 position	Screw	Locking			
785-1TL1-4	1TL1-4	F	SPST	(OFF)-ON	2 position	Screw	Standard			
785-1TL1-5	1TL1-5	F	SPDT	(ON)-OFF-ON	3 position	Screw	Standard			
785-1TL1-6	1TL1-6	F	SPST	(ON)-OFF	2 position	Screw	Standard			
785-1TL1-7	1TL1-7	F	SPDT	(ON)-OFF-(ON)	3 position	Screw	Standard			
785-1TL1-7L	1TL1-7L	F	SPDT	(ON)-OFF-(ON)	3 position	Screw	Locking			
785-1TL1-8	1TL1-8	F	SPDT	ON-ON	2 position	Screw	Standard			
785-1TL1-8F	1TL1-8F	F	SPDT	ON-ON	2 position	Screw	Locking			
785-1TW1-3	1TW1-3	G	SPDT	ON-ON	2 position	Solder	Standard			
785-2NT1-1	2NT1-1	H	DPDT	ON-OFF-ON	3 position	Screw	Standard			
785-2NT1-2	2NT1-2	H	DPST	OFF-ON	2 position	Screw	Standard			
785-2NT1-3	2NT1-3	H	DPDT	ON-ON	2 position	Screw	Standard			
785-2NT1-50	2NT1-50	H	DPDT	(ON)-ON-ON	3 position	Screw	Standard			
785-2NT1-7	2NT1-7	H	DPDT	(ON)-OFF-(ON)	3 position	Screw	Standard			
785-2NT1-70	2NT1-70	H	DPDT	(ON)-ON-(ON)	3 position	Screw	Standard			
785-2NT1-8	2NT1-8	H	DPDT	ON-ON	2 position	Screw	Standard			
785-2TL1-1A	2TL1-1A	H	DPDT	ON-OFF-ON	3 position	Screw	Locking			
785-2TL1-1E	2TL1-1E	H	DPDT	ON-OFF-ON	3 position	Screw	Locking			
785-2TL1-2D	2TL1-2D	H	DPST	OFF-ON	2 position	Screw	Locking			
785-2TL1-3D	2TL1-3D	H	DPDT	ON-ON	3 position	Screw	Locking			
785-2TL1-3G	2TL1-3G	H	DPDT	ON-ON	2 position	Screw	Locking			
785-2TL1-6F	2TL1-6F	H	DPST	(ON)-OFF	2 position	Screw	Locking			
785-2TL1-7E	2TL1-7E	H	DPDT	(ON)-OFF-(ON)	3 position	Screw	Locking			
785-4TL1-3D	4TL1-3D	H	4PDT	ON-ON	2 position	Screw	Locking			
785-4TL1-7	4TL1-7	H	4PDT	(ON)-OFF-(ON)	3 position	Screw	Standard			
785-2TL1-1	2TL1-1	I	DPDT	ON-OFF-ON	3 position	Screw	Standard			
785-2TL1-10	2TL1-10	I	DPDT	ON-ON-ON	3 position	Screw	Standard			
785-2TL1-10A	2TL1-10A	I	DPDT	ON-ON-ON	3 position	Screw	Locking			
785-2TL1-2	2TL1-2	I	DPST	OFF-ON	2 position	Screw	Standard			
785-2TL1-3	2TL1-3	I	DPDT	ON-ON	3 position	Screw	Standard			
785-2TL1-4	2TL1-4	I	DPST	(OFF)-ON	2 position	Screw	Standard			
785-2TL1-5	2TL1-5	I	DPDT	(ON)-OFF-ON	3 position	Screw	Standard			
785-2TL1-50	2TL1-50	I	DPDT	(ON)-ON-ON	3 position	Screw	Standard			
785-2TL1-7	2TL1-7	I	DPDT	(ON)-OFF-(ON)	3 position	Screw	Standard			
785-2TL1-70	2TL1-70	I	DPDT	(ON)-ON-(ON)	3 position	Screw	Standard			
785-4NT1-1	4NT1-1	I	4PDT	ON-OFF-ON	3 position	Screw	Standard			
785-4NT1-3	4NT1-3	I	4PDT	ON-ON	2 position	Screw	Standard			
785-4NT1-7	4NT1-7	I	4PDT	ON-OFF-ON	3 position	Screw	Standard			
785-4TL1-1	4TL1-1	I	4PDT	ON-OFF-ON	3 position	Screw	Standard			
785-4TL1-12	4TL1-12	I	4PDT	ON-ON-ON	3 position	Screw	Standard			
785-4TL1-2	4TL1-2	I	4PST	OFF-ON	2 position	Screw	Standard			
785-4TL1-3	4TL1-3	I	4PDT	ON-ON	2 position	Screw	Standard			
785-4TL1-5	4TL1-5	I	4PDT	(ON)-OFF-ON	3 position	Screw	Standard			
785-4TL1-72	4TL1-72	I	4PDT	(ON)-ON-(ON)	3 position	Screw	Standard			
785-4TL1-8	4TL1-8	I	4PDT	(ON)-ON	2 position	Screw	Standard			
785-61NT1-2	61NT1-2	I	SPST	OFF-ON	2 position	Screw	Standard			
785-2TW1-3	2TW1-3	J	DPDT	ON-ON	2 position	Solder	Standard			
785-31NT391-7-C08	31NT391-7-C08	K	SPDT	(ON)-OFF-(ON)	3 position	Quick Connect	Tab			
785-31NT91-2	31NT91-2	L	SPST	OFF-ON	2 position	Quick Connect	Standard			
785-31NT91-3	31NT91-3	L	SPDT	ON-ON	2 position	Quick Connect	Standard			
785-31NT91-7	31NT91-7	L	SPDT	(ON)-OFF-(ON)	3 position	Quick Connect	Standard			
785-32NT91-70	32NT91-70	L	DPDT	(ON)-ON-(ON)	3 position	Quick Connect	Standard			
785-32NT91-1	32NT91-1	M	DPDT	ON-OFF-ON	3 position	Quick Connect	Standard			
785-32NT91-2	32NT91-2	M	DPST	OFF-ON	2 position	Quick Connect	Standard			
785-32NT91-3	32NT91-3	M	DPDT	ON-ON	2 position	Quick Connect	Standard			
785-32NT91-7	32NT91-7	M	DPDT	(ON)-OFF-(ON)	3 position	Quick Connect	Standard			



Honeywell Toggle Switches