

# AMP Tools and Accessories

## TOOLS FOR PCB CONNECTORS AND PIN AND SOCKET CONNECTORS

### Pro Crimper III Hand Tool

- Field repair / prototyping
- Ratchet control
- Brush / bellmouth control
- Precision crimp height control

MOUSER STOCK NO.	Fig.	Description	Price Each
571-908721	A	.093" Pin and Socket cont. 24-18 AWG	
571-908711	A	.093" Pin and Socket cont. 20-14 AWG	
571-908701	A	.062" Pin and Socket cont. 30-24 AWG	
571-908691	A	.062" Pin and Socket cont. 24-18 AWG	
571-585141	A	Miniature rectangular connectors	
571-905741	A	Commercial Mate-N-Lok® 24-18 AWG	
571-905751	A	Commercial Mate-N-Lok® 20-14 AWG	
571-905481	A	Universal Mate-N-Lok® 24-18 AWG	
571-905461	A	Universal Mate-N-Lok® 20-14 AWG	
571-584951	A	"Series 1" CPC size 16 contacts	
571-584482	A	"Series 2" CPC size 20 contacts	
571-3549401	A	Pro-Crimper III frame	
571-584231	A	Die set for solderless terminals	

### Certi-Crimp Crimping Tool

- Field repair / prototyping
- Ratchet control
- Brush / bellmouth control
- Precision crimp height control

MOUSER STOCK NO.	Fig.	Description	Price Each
571-903822	B	"Series 3" CPC type XII 12-16 AWG	
571-903841	B	"Series 3" CPC type XII 8-10 AWG	

## TOOLS FOR MTA SERIES

### Pistol Grip Hand Tool

MOUSER STOCK NO.	Fig.	Description	Price Each
571-580741	C	Pistol Grip Hand Tool for MTA Series	

### Interchangeable Head for Pistol Grip Hand Tool

MOUSER STOCK NO.	Fig.	Description	Price Each
571-58246-1	D	MTA .100 Series	
571-582471	D	MTA .156 Series	

### "T" Handle Maintenance Tool

MOUSER STOCK NO.	Fig.	Description	Price Each
571-598031	E	For MTA .100 Series	
571-598041	E	For MTA .156 Series	

## CONTACT INSERTION/EXTRACTION TOOLS

MOUSER STOCK NO.	Fig.	Description	Price Each
571-910672	F	Insertion/extraction, size 20, 22 contacts	
571-3188311	G	Extraction, .062 Pin and Socket	
571-1804030-1	G	Extraction, Universal Mate-N-Lok®	
571-4558301	H	Insertion, Universal Mate-N-Lok® and MR	
571-4558222	I	Extraction, Miniature Rectangular	
571-4656441	J	Extraction, Commercial Mate-N-Lok®	
571-305183	K	Extraction, size 16 CPC contacts	
571-912851	L	Insertion/extraction, size 20, 22 contacts	
571-910193	M	Extraction, type XII series 3 CPC contacts	
571-911241	N	Extraction, type XII series 4 CPC contacts	

## TOOLS FOR MODULAR PLUGS

### "Category 5" High Performance Crimp Tool

- For use with modular plugs
- Cuts, strips, and terminates cable
- All plug sizes, except 10-position are accommodated using interchangeable die sets

MOUSER STOCK NO.	Fig.	Description	Price Each
571-32316520	O	8-position modular crimp tool with die	

### Professional Hand Tools with Die Sets

- For use with modular plugs
- Cuts, strips, and terminates cable
- All plug sizes, except 10-position are accommodated using interchangeable die sets


571-22316521	O	8-position line	
571-22316523	O	4-position handset	
571-2-231652-6	O	6-position offset-latch	
571-22316527	O	6-position long body	
571-22316528	O	4, 6-position line	

### Die Set Only for Professional Hand Tool

571-8534001	-	8-position line	
571-8534003	-	4-position handset	
571-853400-6	-	6-position offset-latch	
571-8534007	-	6-position long body	
571-853400-8	-	4,6-position line	

### Professional Hand Tool Kits

571-12316661	-	4-position handset, 4, 6, and 8-position die sets, set of replacement strip blades and small screwdriver	
571-2316625	-	(1) set of strip blades	



AMP Hand Tools