

REAN Control Knobs

REAN



This page of product is compliant.

PUSH-FIT ONE PIECE CONTROL KNOBS

- Black knobs with color coded marker lines
- Available to fit either D flat or 6mm spline shafts
- Knobs available with Soft Touch or Hard Nylon surface material

For quantities of 100 and up, call for quote.

MOUSER STOCK NO.	Rean Part No.	Fig.	Surface Material	Line Color	Orientation	Size (mm)		Price Each		
						Dia.	Ht.	1	10	25
550-P400S-02-S6	P400S-02-S6	A1	Soft Touch	Red	-	10	16.5			
550-P400S-04-S6	P400S-04-S6	A1	Soft Touch	Yellow	-	10	16.5			
550-40004	P400S-06-D6S	A2	Soft Touch	Blue	South	10	16.5			
550-40106	P400S-06-S6	A1	Soft Touch	Blue	-	10	16.5			
550-40009	P400S-09-S-6	A1	Soft Touch	White	-	10	16.5			
550-57002	P570H-02-S6	B1	Hard Nylon	Red	-	11	14.6			
550-57006	P570H-06-S6	B1	Hard Nylon	Blue	-	11	14.6			
550-P570-76	P570H-08-S6	B1	Hard Nylon	Gray	-	11	14.6			
550-57001	P570H-09-S6	B1	Hard Nylon	White	-	11	14.6			
550-67021	P670S-02-D6N	C2	Soft Touch	Red	North	11.5	14.4			
550-67041	P670S-04-D6N	C2	Soft Touch	Yellow	North	11.5	14.4			
550-67002	P670S-06-D6-N	C2	Soft Touch	Blue	North	11.5	14.4			
550-67004	P670S-06-S6	C1	Soft Touch	Blue	-	11.5	14.4			
550-67001	P670S-08-D6N	C2	Soft Touch	Gray	North	11.5	14.4			
550-67081	P670S-08-D6S	C2	Soft Touch	Gray	South	11.5	14.4			
550-67003	P670S-08-S6	C1	Soft Touch	Gray	-	11.5	14.4			
550-67092	P670-S-09-D25-S	C3	Soft Touch	White	South	11.5	14.4			
550-67091	P670S-09-D6N	C2	Soft Touch	White	North	11.5	14.4			
550-P82-90F	P670S-09-D6S	C2	Soft Touch	White	South	11.5	14.4			
550-67005	P670S-09-S6	C1	Soft Touch	White	-	11.5	14.4			
550-P675S-09-D6S	P675S-09-D6S	D2	Soft Touch	White	South	11.5	13.5			

PUSH-FIT TWO PIECE CONTROL KNOBS

- Add more flexibility with a two color knob and color coded cap
- Surface material is Hard Nylon unless otherwise noted
- Color coded caps sold separately (see below)

For quantities of 100 and up, call for quote.

MOUSER STOCK NO.	Rean Part No.	Fig.	Body Color	Line Color	Orientation	Size (mm)		Price Each		
						Dia.	Ht.	1	10	25
550-15031	P150-H-09-D25-N	E3	Black	White	North	15	13.5			
550-86103	P861-H-0-D25	F3	Black	-	-	19	19			
550-86102	P861H-0X-S6	F1	Black	-	-	19	19			

COLLET KNOBS

- Features a screw-fix fitting that allows freedom when selecting marker line orientation
- Surface material is Hard Nylon unless otherwise noted
- Color coded caps sold separately (see below)

For quantities of 100 and up, call for quote.

MOUSER STOCK NO.	Rean Part No.	Fig.	Body Color	Line Color	Shaft Size	Size (mm)		Price Each		
						Dia.	Ht.	1	10	25
550-10501	C100-H-09-R12	G	Black	White	1/8"	10	13.5			
550-C15009	C150H-09-R012	H	Black	White	1/8"	15	13.5			
550-15001	C150-H-09-R25	H	Black	White	1/4"	15	13.5			
550-15601	C150H-09-R6	H	Black	White	6mm	15	13.5			
550-15002	C210H-09-R012	I	Black	White	1/8"	21	17			

CAPS

- Color coded caps for Push-Fit and Collet Knobs

For quantities of 100 and up, call for quote.

MOUSER STOCK NO.	Rean Part No.	Fig.	Body Color	Line Color	Fits Series	Size (mm)		Price Each		
						Dia.	Ht.	1	10	25
550-10001	T100-H-09	J	Black	White	P/C100	10				
550-10011	T100-H-0X	K	Black	-	P/C100	10				
550-10003	T100-H-69	J	Blue	White	P/C100	10				
550-10002	T100-H-89	J	Gray	White	P/C100	10				
550-15011	T150-H-09	J	Black	White	P/C150	15				
550-15021	T150-H-0X	K	Black	-	P/C150	15				
550-15029	T150-H-29	J	Red	White	P/C150	15				
550-15013	T150-H-69	J	Blue	White	P/C150	15				
550-15023	T150-H-6X	K	Blue	-	P/C150	15				
550-15012	T150H-89	J	Gray	White	P/C150	15				
550-15022	T150-H-8X	K	Gray	-	P/C150	15				
550-86301	T890H-09	J	Black	White	P861,P890	19				
550-86302	T890H-69	J	Blue	White	P861,P890	19				
550-86303	T890H-89	J	Gray	White	P861,P890	19				

SLIDE CONTROL KNOBS

- Ergonomics and Aesthetics at a competitive price
- All Sliders have molded in marker lines that help eliminate fade
- Surface material is Hard Nylon unless otherwise noted

For quantities of 100 and up, call for quote.

MOUSER STOCK NO.	Rean Part No.	Fig.	Body Color	Line Color	Width (mm)	Price Each		
						1	10	25
550-S771H-90-M	S771H-90-M	L4	White	Black	-			
550-77301	S773H-09-K	M5	Black	White	11			
550-77304	S773H-09-M	M5	Black	White	11			
550-77309	S773H-09-P	M6	Black	White	11			
550-77201	S773H-90-K	M5	White	Black	11			
550-77801	S778H-09-K	N5	Black	White	15			
550-77804	S778H-09-M	N4	Black	White	15			
550-S778H-09-P	S778H-09-P	N6	Black	White	15			

DIMENSIONS: mm