

TOOL MATRIX

Crimping Tool	Insertion Tool	Extraction Tool	Use With Connector Series
63811-0200 63811-0300		57072-6000	1.25mm Crimp Terminal
63811-4800			1.27mm Micro-D
11-01-0185 63811-3300 63811-1000	11-02-0001	11-03-0002	.062" Pin and Socket
63811-6800		11-01-0168	.084" Pin and Socket
63811-1000 63811-3200	11-02-0003	11-03-0006	.093" Pin and Socket
11-01-0204			2mm Milli-Grid™ Crimp Terminal
63811-8700 11-01-0209	11-02-0022	11-03-0036	2.54mm SL™
11-01-0206		11-03-0037	Disk Drive
11-01-0185	63812-0000	11-03-0022	KK-100
11-01-0185 63811-7500 11-01-0203		11-03-0016	KK-156
63811-2800		11-03-0043	Micro-Fit 3.0™
6381-5000 11-01-0197 11-01-0198		11-03-0044	Mini-Fit™ Jr.
63811-1500 63811-1600		63813-0400	Mini-Fit™ Sr.
63811-4400		63813-1500	MX150L™
63811-7200		63813-0500	Sabre™ 7.5mm (Female)
63811-0600		63813-0800	Sabre™ 7.5mm (Male)

INSERTION AND EXTRACTION TOOLS

MOUSER STOCK NO.	Fig.	Description	Price Each
538-11-02-0001	A	.062" Pin and Socket Insertion Tool	
538-11-03-0002	B	.062" Pin and Socket Extraction Tool	
538-11-01-0168	C	.084" Pin and Socket Extraction Tool	
538-11-02-0003	A	.093" Pin and Socket Insertion Tool	
538-11-03-0006	B	.093" Pin and Socket Extraction Tool	
538-11-02-0022	D	2.54mm SL™ Insertion Tool	
538-11-03-0036	B	2.54mm SL™ Extraction Tool	
538-11-03-0037	B	Disk Drive Extraction Tool	
538-63812-0000	B	KK-100 Insertion Tool	
538-11-03-0022	E	KK-100 Extraction Tool	
538-11-03-0016	F	KK-156 Extraction Tool	
538-11-03-0043	G	Micro-Fit 3.0™ Extraction Tool	
538-11-03-0044	G	Mini-Fit™ Jr. Extraction Tool	
538-63813-0400	H	Mini-Fit™ Sr. Extraction Tool	
538-63813-1500	I	MX150L™ Extraction Tool	
538-63813-2700	F	Sabre™ 7.5mm (Female) Extraction Tool	
538-63813-0800	J	Sabre™ 7.5mm (Male) Extraction Tool	

TOOLS FOR PCB AND PIN AND SOCKET CONNECTORS

MOUSER STOCK NO.	Fig.	Description	Price Each
538-63819-0300	K	1.25mm Crimp Terminal 32-26 AWG	
538-63811-4800	K	1.27mm Micro-D 28-26 AWG	
538-63819-0800	K	.062" Pin and Socket 30-22 AWG	
538-63819-1300	L	.062" Pin and Socket 24-18 AWG	
538-63811-1000	M	.062" & .093" Pin and Socket 24-14 AWG	
538-63811-6800	N	.084" Pin and Socket 20-14 AWG	
538-63819-1200	L	.093" Pin and Socket 22-14 AWG	
538-63819-0100	K	2mm Crimp Terminal	
538-63819-0500	K	2mm Crimp Terminal	
538-63819-0100	K	2mm Milli-Grid™ Crimp Terminal 30-24 AWG	
538-63811-5200	K	2.50 Spox Crimp Terminal	
538-63811-8700	K	2.54mm SL™ 24-22 AWG	
538-638118800	K	2.54mm SL™ 30-24 AWG	
538-63811-7000	K	Disk Drive 22-14 AWG	
538-63811-7500	K	KK-156 24-18 AWG	
538-63811-6600	K	KK-156 30-18 AWG	
538-63819-0000	K	Micro-Fit 3.0™ 30-20 AWG	
538-63811-2875	-	Crimp Tool Locator for 538-63811-2800	
538-63819-0900	K	Mini-Fit™ Jr. 24-18 AWG	
538-63819-1000	K	Mini-Fit™ Jr. 28-22 AWG	
538-63811-1500	O	Mini-Fit™ Sr. 8 AWG	
538-63811-1600	O	Mini-Fit™ Sr. 12-10 AWG	
538-63811-4400	O	MX150L™ 22-14 AWG	
538-63811-7200	N	Sabre™ 7.5mm (Female) 18-14 AWG	

