

MURATA Hi-Cap Multilayer Ceramic Chip Capacitors

RoHS Compliant This product is RoHS compliant.



0805 CASE SIZE (CONT.)

MOUSER STOCK NO.	Murata Part No.	Value (µF)	Volt (DC)	Tol.±	Temperature Coefficient	Price Each				Reel Quantity	Price per Piece
						1	50	100	500		
81-GRM40034R475K6L	GRM21BR60J475KA11L	4.7	6.3	10%	X5R					3000	
81-GRM21BR61A475KA73	GRM21BR61A475KA73L	4.7	10	10%	X5R					3000	
81-GRM21BR61E475KA12	GRM21BR61E475KA12L	4.7	25	10%	X5R					3000	
81-GRM21BR71C475KA73	GRM21BR71C475KA73L	4.7	16	10%	X7R					3000	
81-GRM40Y5V475Z010AL	GRM21BF51A475ZA01L	4.7	10	+80% -20%	Y5V					3000	
81-GRM21BF51E475ZA01	GRM21BF51E475ZA01L	4.7	25	+80% -20%	Y5V					3000	
81-GRM21BR60J106ME19	GRM21BR60J106ME19L	10	6.3	20%	X5R					3000	
81-GRM21R60J106KE19L	GRM21BR60J106KE19L	10	6.3	10%	X5R					3000	
81-GRM21BR61A106KE19	GRM21BR61A106KE19L	10	10	10%	X5R					3000	
81-GRM21BR70J106KE76	GRM21BR70J106KE76L	10	6.3	10%	X7R					3000	
81-GRM21BR71A106KE51	GRM21BR71A106KE51L	10	10	10%	X7R					3000	
81-GRM21F50J106ZE01L	GRM21BF50J106ZE01L	10	6.3	+80% -20%	Y5V					3000	
81-GRM21F51A106ZE15L	GRM21BF51A106ZE15L	10	10	+80% -20%	Y5V					3000	
81-GRM21BF51C106ZE15L	GRM21BF51C106ZE15L	10	16	+80% -20%	Y5V					3000	

1206 CASE SIZE

81-GRM426X105K16L	GRM31MR71C105KA01L	1.0	16	10%	X7R					3000	
81-GRM31MR71E105KA01	GRM31MR71E105KA01L	1.0	25	10%	X7R					3000	
81-GRM31CR71H105KA61L	GRM31CR71H105KA61L	1.0	50	10%	X7R					2000	
81-GRM31MR71H105KA88L	GRM31MR71H105KA88L	1.0	50	10%	X7R					3000	
81-GRM31CR72A105KA01	GRM31CR72A105KA01L	1.0	100	10%	X7R					2000	
81-GRM319F51C105ZA01	GRM319F51C105ZA01D	1.0	16	+80% -20%	Y5V					4000	
81-GRM426Y105Z25L	GRM31MF51E105ZA01L	1.0	25	+80% -20%	Y5V					3000	
81-GRM426X225K010L	GRM31MR71A225KA01L	2.2	10	10%	X7R					3000	
81-GRM426X225K16L	GRM31MR71C225KA35L	2.2	16	10%	X7R					3000	
81-GRM31R71E225KA93L	GRM31MR71E225KA93L	2.2	25	10%	X7R					3000	
81-GRM31CR71H225KA88L	GRM31CR71H225KA88L	2.2	50	10%	X7R					2000	
81-GRM426Y5V225Z	GRM31MF51C225ZA01L	2.2	16	+80% -20%	Y5V					3000	
81-GRM31MF51E225Z	GRM31MF51E225ZA12L	2.2	25	+80% -20%	Y5V					3000	
81-GRM426R475K10L	GRM31CR61A475KA01L	4.7	10	10%	X5R					2000	
81-GRM31CR61C475KA	GRM31CR61C475KA01L	4.7	16	10%	X5R					2000	
81-GRM426X475K10L	GRM31CR71A475KA01L	4.7	10	10%	X7R					2000	
81-GRM31CR71E475KA88	GRM31CR71E475KA88L	4.7	25	10%	X7R					2000	
81-GRM31F51A475ZA01L	GRM31MF51A475ZA01L	4.7	10	+80% -20%	Y5V					3000	
81-GRM31MF51C475Z	GRM31MF51C475ZA01L	4.7	16	+80% -20%	Y5V					3000	
81-GRM31F51H475ZA01L	GRM31CF51H475ZA01L	4.7	50	+80% -20%	Y5V					2000	
81-GRM31R60J106KA01L	GRM31CR60J106KA01L	10	6.3	10%	X5R					2000	
81-GRM426R106K10L	GRM31CR61A106KA01L	10	10	10%	X5R					2000	
81-GRM31MR61A106KE19	GRM31MR61A106KE19L	10	10	10%	X5R					3000	
81-GRM31CR61C106KA88	GRM31CR61C106KA88L	10	16	10%	X5R					2000	
81-GRM31R61E106KA12L	GRM31CR61E106KA12L	10	25	10%	X5R					2000	
81-GRM426X106K6.3L	GRM31CR70J106KA01L	10	6.3	10%	X7R					2000	
81-GRM31CR71A106KA01	GRM31CR71A106KA01L	10	10	10%	X7R					2000	
81-GRM426Y106Z10L	GRM31MF51A106ZA01L	10	10	+80% -20%	Y5V					3000	
81-GRM31MF51C106ZA12	GRM31MF51C106ZA12L	10	16	+80% -20%	Y5V					3000	
81-GRM31CF51E106ZA01	GRM31CF51E106ZA01L	10	25	+80% -20%	Y5V					2000	
81-GRM31R60J226ME19L	GRM31CR60J226ME19L	22	6.3	20%	X5R					2000	
81-GRM31CR60J226KE19	GRM31CR60J226KE19L	22	6.3	10%	X5R					2000	
81-GRM31CF51A226ZE01	GRM31CF51A226ZE01L	22	10	+80% -20%	Y5V					2000	
81-GRM426X476M6.3L	GRM31CR60J476ME19L	47	6.3	20%	X5R					2000	

1210 CASE SIZE

MOUSER STOCK NO.	Murata Part No.	Value (µF)	Volt (DC)	Tol.±	Temperature Coefficient	Price Each				Reel Quantity	Price per Piece
						1	50	100	500		
81-GRM422X105K50K	GRM32RR71H105KA01K	1.0	50	10%	X7R					4000	
81-GRM422X105K50L	GRM32RR71H105KA01L	1.0	50	10%	X7R					1000	
81-GRM32ER72A105KA01	GRM32ER72A105KA01L	1.0	100	10%	X7R					1000	
81-GRM422X225K16L	GRM32MR71C225KC01L	2.2	16	10%	X7R					3000	
81-GRM32ER72A225KA35	GRM32ER72A225KA35L	2.2	100	10%	X7R					1000	
81-GRM32RR61E475KA12	GRM32RR61E475KA12L	4.7	25	10%	X5R					1000	
81-GRM32R71H475KA88L	GRM32ER71H475KA88L	4.7	50	10%	X7R					1000	
81-GRM422R106K10L	GRM32ER61A106KA01L	10	10	10%	X5R					1000	
81-GRM32R71C106KA01L	GRM32DR71C106KA01L	10	16	10%	X7R					1000	
81-GRM32DR71E106KA12	GRM32DR71E106KA12L	10	25	10%	X7R					1000	
81-GRM422Y106Z16L	GRM32NF51C106ZA01L	10	16	+80% -20%	Y5V					2000	
81-GRM32NF51E106ZA01	GRM32NF51E106ZA01L	10	25	+80% -20%	Y5V					2000	
81-GRM32DF51H106ZA01	GRM32DF51H106ZA01L	10	50	+80% -20%	Y5V					2000	
81-GRM32ER61C226KE20	GRM32ER61C226KE20L	22	16	10%	X5R					1000	
81-GRM32R71A226KE20L	GRM32ER71A226KE20L	22	10	10%	X7R					1000	
81-GRM32CF51A226ZA01	GRM32CF51A226ZA01L	22	10	+80% -20%	Y5V					2000	
81-GRM32CF51C226ZA12	GRM32CF51C226ZA12L	22	16	+80% -20%	Y5V					1000	
81-GRM32ER60J476ME20	GRM32ER60J476ME20L	47	6.3	20%	X5R					1000	
81-GRM32ER60J107ME20	GRM32ER60J107ME20L	100	6.3	20%	X5R					1000	
81-GRM32EF50J107ZE20	GRM32EF50J107ZE20L	100	6.3	+80% -20%	Y5V					1000	

1812 CASE SIZE

81-GRM432X7R225K50	GRM43ER71H225KA01L	2.2	50	10%	X7R					500	
81-GRM43ER72A225KA01	GRM43ER72A225KA01L	2.2	100	10%	X7R					500	
81-GRM43ER61C226KE01	GRM43ER61C226KE01L	22	16	10%	X5R					1000	
81-GRM43ER60J476KE01	GRM43ER60J476KE01L	47	6.3	10%	X5R					500	
81-GRM43ER61A476KE19	GRM43ER61A476KE19L	47	10	10%	X5R					500	
81-GRM43SR60J107ME20	GRM43SR60J107ME20L	100	6.3	20%	X5R					500	

2220 CASE SIZE

81-GRM55RR71H105KA01	GRM55RR71H105KA01L	1.0	50	10%	X7R					1000	
81-GRM55ER72A475KA01	GRM55ER72A475KA01L	4.7	100	10%	X7R					500	

Murata Ceramic Caps, SMD