


QUALTEK Power Cords

Qualtek ELECTRONICS CORPORATION

Primary Power Components Div.

RoHS Compliant This product is RoHS compliant.



NORTH AMERICAN POWER CORDS

2 Conductor Power Cords

All cords have CEE Color Code (Brown/Blue/Green/Yellow), with 60°C temperature rating unless marked as below:

† North American Color Code (Black/White/Green)
Temperature Rating: 105°C VW-1



MOUSER STOCK NO.	Qualtek Part No.	Fig.	"L"	Cordage	No. of Cond. AWG	Amps 125V	Nema Plug	Conn.	Price Each		
									1	10	25
562-221001-01	221001-01	A	6'0"	SPT-1 †	2 x 18	10	1-15	-	1.92	1.84	1.78
562-221002-01	221002-01	A	9'0"	SPT-1 †	2 x 18	10	1-15	-	2.48	2.30	2.20
562-223020-01	223020-01	B	6'0"	SPT-2 † #	2 x 18	7	1-15	C7	2.10	1.95	1.88
562-223021-01	223021-01	B	8'0"	SPT-2 † #	2 x 18	7	1-15	C7	3.56	3.31	2.97

For quantities greater than listed, call for quote.

3 Conductor Power Cords - Unshielded

All cords have CEE Color Code (Brown/Blue/Green/Yellow), with 60°C temperature rating unless marked as below:

† North American Color Code (Black/White/Green)
Temperature Rating: 105°C VW-1

Features:
• Black: -01
• Gray: -06



MOUSER STOCK NO.	Qualtek Part No.	Fig.	"L"	Cordage	No. of Cond. AWG	Amps 125V	Nema Plug	Conn.	Price Each		
									1	10	25
562-211011-01	211011-01	C	6'0"	SVT †	3 x 18	10	5-15	-	3.38	3.21	3.04
562-211011-06	211011-06	C	6'0"	SVT †	3 x 18	10	5-15	-	4.10	3.81	3.54
562-211012-06	211012-06	C	8'0"	SVT †	3 x 18	10	5-15	-	4.26	4.00	3.75
562-211017-06	211017-06	C	6'0"	SVT †	3 x 18	10	5-15	-	5.34	4.97	4.62
562-211018-06	211018-06	C	8'0"	SVT †	3 x 18	10	5-15	-	3.64	3.48	3.38
562-311010-01	311010-01	C	9'10"	SVT	3 x 18	10	5-15	-	4.85	4.70	4.50
562-311016-01	311016-01	C	9'10"	SJT	3 x 18	10	5-15	-	6.39	5.88	5.40
562-311007-01	311007-01	C	6'7"	SVT	3 x 18	10	5-15	-	3.20	2.88	2.72
562-311013-01	311013-01	C	6'6"	SJT	3 x 18	10	5-15	-	6.35	5.73	5.34
562-311019-01	311019-01	C	6'6"	SJT	3 x 16	13	5-15	-	6.45	5.83	5.28
562-311022-01	311022-01	C	9'8"	SJT	3 x 16	13	5-15	-	9.65	8.70	7.88
562-311027-01	311027-01	C	9'10"	SJT	3 x 14	15	5-15	-	9.65	8.69	8.42
562-212004-01	212004-01	D	7'6"	SVT †	3 x 18	10	5-15	C13	4.50	4.25	4.04
562-212013-01	212013-01	D	7'6"	SJT †	3 x 16	13	5-15	C13	6.11	5.86	5.67
562-312003-01	312003-01	D	7'6"	SVT	3 x 18	10	5-15	C13	4.05	3.88	3.75
562-312007-01	312007-01	D	6'7"	SJT	3 x 18	10	5-15	C13	4.71	3.90	3.64
562-312008-01	312008-01	D	7'6"	SJT	3 x 18	10	5-15	C13	5.30	5.00	4.67
562-312010-01	312010-01	D	9'10"	SJT	3 x 18	10	5-15	C13	6.45	6.12	6.00
562-312011-01	312011-01	D	6'6"	SJT	3 x 16	13	5-15	C13	6.10	5.04	4.43
562-312014-01	312014-01	D	9'10"	SJT	3 x 16	13	5-15	C13	7.00	6.75	6.50
562-312019-01	312019-01	D	9'10"	SJT	3 x 14	15	5-15	C13	8.97	8.18	7.33
562-312021-01	312021-01	D	7'6"	SVT #	3 x 18	10	5-15	C13	4.50	4.27	4.06
562-313001-01	313001-01	E	7'6"	SVT	3 x 18	10	5-15	C13	4.70	4.48	4.16
562-313003-01	313003-01	E	6'7"	SVT	3 x 18	10	5-15	C13	4.80	4.38	4.00
562-313006-01	313006-01	E	6'6"	SJT	3 x 18	10	5-15	C13	5.85	5.36	4.93
562-313011-01	313011-01	E	7'6"	SJT	3 x 16	13	5-15	C13	7.45	7.08	6.69
562-313014-01	313014-01	E	9'10"	SJT	3 x 16	13	5-15	C13	7.32	6.61	6.10
562-315005-01	315005-01	F	6'6"	SJT	3 x 16	10	-	C13	4.90	4.57	4.24
562-315008-01	315008-01	F	9'10"	SJT	3 x 18	10	-	C13	4.80	4.56	4.41

For quantities greater than listed, call for quote.

3 Conductor Power Cords - Unshielded (CONT.)

MOUSER STOCK NO.	Qualtek Part No.	Fig.	"L"	Cord.	No. of Cond. AWG	Amps V	Nema Plug	Conn.	Price Each		
									1	10	25
562-331010-01	331010-01	G	9'10"	SJT	3 x 14	15@250	C20	C19	12.00	11.60	11.20
562-318002-01	318002-01	H	3'3"	SVT	3 x 18	10@125	C14	C13	3.76	3.64	3.29
562-318005-01	318005-01	H	3'3"	SJT	3 x 18	10@125	C14	C13	3.49	3.34	3.09
562-318007-01	318007-01	H	3'3"	SJT	3 x 16	13@125	C14	C13	3.91	3.73	3.63

Hospital Grade - Unshielded

Features:
• With North American Color Code (Black/White/Green)
• Cordage: SJT
• Temperature rating: 60°C

* Hospital Grade Clear Plug
** Hospital Grade Gray Plug
†† Hospital Grade Black Plug
‡ Right Angle Plug



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Qualtek Part No.	Fig.	"L"	Cord. Color	No. of Cond. AWG	Amps 125V	Nema Plug	Conn.	Price Each		
									1	10	25
* 562-232002-06	232002-06	I	8'0"	Gray	3 x 18	10	5-15	-	6.30	5.98	5.85
* 562-232003-06	232003-06	I	10'0"	Gray	3 x 18	10	5-15	-	9.06	8.60	8.39
** 562-232010-06	232010-06	I	8'0"	Gray	3 x 18	10	5-15	-	5.67	5.37	5.11
** 562-232011-06	232011-06	I	10'0"	Gray	3 x 18	10	5-15	-	7.45	7.15	6.70
* 562-233002-06	233002-06	J	8'0"	Gray	3 x 18	10	5-15	C13	6.23	6.00	5.72
* 562-233003-06	233003-06	J	10'0"	Gray	3 x 18	10	5-15	C13	11.04	10.48	9.96
** 562-233008-06	233008-06	J	8'0"	Gray	3 x 18	10	5-15	C13	6.62	6.29	6.00
** 562-233009-06	233009-06	J	10'0"	Gray	3 x 18	10	5-15	C13	6.95	6.60	6.27
†† 562-242003-06	242003-06	K	10'0"	Gray	3 x 18	10	5-15	-	5.72	5.54	5.16
‡ 562-243003-06	243003-06	L	10'0"	Gray	3 x 18	10	5-15	C13	12.50	11.35	10.78
** 562-233080-06	233080-06	M	10'0"	Gray	3 x 12	20	5-15	C19	18.27	17.44	16.61
* 562-233081-06	233081-06	N	10'0"	Gray	3 x 12	20	5-20	C19	18.27	17.44	16.61
* 562-233082-06	233082-06	M	10'0"	Gray	3 x 14	15	5-15	C19	13.99	13.35	12.72
* 562-233056-06	233056-06	J	10'0"	Gray	3 x 16	13	5-15	C13	8.97	8.56	8.15
†† 562-233058-01	233058-01	J	10'0"	Black	3 x 16	13	5-15	C13	8.97	8.56	8.15

Twist Lock Power Cord - Unshielded

Features:
• With North American Color Code (Black/White/Green)
• Cordage: SJT
• Temperature rating: 60°C

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Qualtek Part No.	Fig.	"L"	Cord. Color	No. of Cond. AWG	Amps 125V	Plug	Conn.	Price Each		
									1	10	25
562-250069-01	250069-01	O	10'0"	Black	3 x 16	13	L5-15P	L5-15R	13.65	13.03	12.41

Universal Jumper Cords

Features:
• CEE Color Code
• Cordage: SJT/H05VV-F
• Temperature rating: 60°C

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Qualtek Part No.	Fig.	"L"	Cord. Color	No. of Cond. AWG	Amps 250V	Plug	Conn.	Price Each		
									1	10	25
562-319002	319002-T01	H	3'3"	Black	3 x 18/3 x 1.0mm ²	10.0	C14	C13	4.40	4.25	3.83
562-319004	319004-T01	H	8'2"	Black	3 x 18/3 x 1.0mm ²	10.0	C14	C13	6.29	6.00	5.62

SAFETY RETAINER CLIPS

Helps prevent accidental removal of detachable power cordsets from IEC 320-C14 Power Inlets and IEC 320-C13 Outlets.

Kit contains: 1 stainless steel clip; 2 threaded posts; 2 threaded nuts; 2 washers

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Qualtek Part No.	Description	Price Each		
			1	10	25
562-730B-01	730B-00/00	Used on power cord Fig. D, F, and H in conjunction with a screw mount IEC power inlet	2.49	2.22	2.04
562-730B-05	730B-00/05	Used on power cord Fig. D, F, and H in conjunction with a screw mount IEC power inlet	2.56	2.31	1.94
562-731B-00	731B-00/00	Used on power cord Fig. J or L in conjunction with a screw mount IEC power inlet	3.25	2.90	2.73
562-732B-00	732B-00/00	Used on power cord Fig. H in conjunction with a screw mount IEC power inlet	3.18	2.95	2.75

