TECHNICAL DATA SHEET

HellermannTyton

Part No. 166-90820
Article No. 166-90820
Type HGU21-45M-M20B



Straight snap-on style fittings with nickel plated brass metric threaded fitting provides a true, one-piece component solution; seals are integrated into the fitting body. Durable nylon materials deliver high chemical resistance against salts, oils, weak acids and solvents. Designed for fast assembly and easy removal using a small screwdriver.

Material	Nickel Plated Brass (NPB), Polyamide 6.6 (PA66)
Operating Temperature	-58°F to +275°F (-50°C to +135°C)
Halogen Free	Yes
IP-Rating	IP68
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)

Pkg. Qty.	10
Carton Qty.	50
Customs Number	7412200000

Length (imperial)	2.99 "
Length (metric)	76 mm
Nominal Diameter (imperial)	0.5 "
Nominal Diameter (metric)	21 mm
Outside Diameter (imperial)	1.26 "
Outside Diameter (metric)	32.0 mm

HF ✓ RoHS ✓