

# SCHURTER AC Inlets, AC Outlets and DC Power Entry Modules

## SCHURTER AC INLETS/OUTLETS

• Rating: 250VAC@15A UL/CSA, 10A VDE/SEMKO



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Schurter Part No.	Fig.	Mounting	Terminals	Price Each			
					1	25	50	100
693-4300.0301	4300.0301	A	Snap-in	4.8x0.8mm Q.C.	3.92	3.49	3.15	2.98
693-4304.6001	4304.6001	B	Vertical Screw-on	Solder	5.90	5.43	4.99	4.68
693-4304.6002	4304.6002	B	Vertical Screw-on	6.3x0.8mm Q.C.	4.25	3.71	3.20	2.95
693-4304.6003	4304.6003	C	Horizontal Screw-on	Solder	4.55	3.98	3.43	3.16
693-4304.6004	4304.6004	C	Horizontal Screw-on	6.3x0.8mm Q.C.	4.05	3.54	3.05	2.81

## SCHURTER INLET WITH SWITCH, FUSEHOLDER

ELECTRONIC COMPONENTS



• Rating: 250VAC@1-10A cURus, ENEC10

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Schurter Part No.	Fig.	Mounting	Terminals	Price Each			
					1	25	50	100
693-4304.6090	4304.6090	D	Horizontal Screw-on	4.8x0.8mm Q.C.	10.35	9.20	8.52	7.37

## SCHURTER INLET WITH SWITCH, FUSEHOLDER, 1- OR 2-STAGE EMI FILTER

ELECTRONIC COMPONENTS



• Rating: 250VAC@1-10A cURus, ENEC10

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Schurter Part No.	Fig.	I <sub>N</sub> (A)	Stages	Mounting	Terminals	Price Each			
							1	25	50	100
693-4304.4022	4304.4022	E	2	1	Horizontal Screw-on	6.3x0.8mm Q.C.	76.51	62.91	54.41	53.31
693-4304.4024	4304.4024	E	6	1	Horizontal Screw-on	6.3x0.8mm Q.C.	68.01	55.93	48.37	47.39
693-4304.4025	4304.4025	E	10	1	Horizontal Screw-on	6.3x0.8mm Q.C.	76.51	62.91	54.41	53.31
693-4304.5021	4304.5021	F	1	2	Horizontal Screw-on	6.3x0.8mm Q.C.	91.22	75.00	64.86	63.55
693-4304.5023	4304.5023	F	4	2	Horizontal Screw-on	6.3x0.8mm Q.C.	86.88	71.43	61.78	60.53
693-4304.5024	4304.5024	F	6	2	Horizontal Screw-on	6.3x0.8mm Q.C.	77.23	63.50	54.92	53.81

## SCHURTER BACKPLANE OUTLETS

ELECTRONIC COMPONENTS



• Rating: 250VAC@15A UL/CSA, 10A VDE

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Schurter Part No.	Fig.	Mounting	Terminals	Price Each			
					1	25	50	100
693-4787.1000	4787.1000	G	Screw-on	6.3x0.8mm Q.C.	2.27	2.02	1.88	1.62
693-4788.8000	4788.8000	H	Snap-in, 1.2mm	6.3x0.8mm Q.C.	2.67	2.38	2.21	1.91
693-4788.4000	4788.4000	H	Snap-in, 1.5mm	6.3x0.8mm Q.C.	2.67	2.38	2.21	1.91
693-4788.5000	4788.5000	H	Snap-in, 2.0mm	6.3x0.8mm Q.C.	2.67	2.38	2.21	1.91
693-4788.6000	4788.6000	H	Snap-in, 2.5mm	6.3x0.8mm Q.C.	2.61	2.38	2.19	2.01

## SCHURTER HIGH CURRENT AC CONNECTORS

ELECTRONIC COMPONENTS



• Rating: 250VAC@21A UL/CSA, 16A VDE/ENEC05

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Schurter Part No.	Fig.	Mounting	Terminals	Price Each			
					1	25	50	100
693-6183.0004	6183.0004	I	Screw-on	6.3x0.8mm Q.C.	5.73	5.19	4.87	4.62
693-6163.0018	6163.0018	J	PCB	PCB+6.3x0.8mm	2.36	2.15	1.97	1.82

## SCHURTER DC FILTERED POWER ENTRY MODULES

ELECTRONIC COMPONENTS




• Rating: 125VDC@3-15A • Terminals: 6.3x0.8mm QC

\* Mounting holes are pre-threaded

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Schurter Part No.	Fig.	I <sub>N</sub> (A)	Mounting Type	Housing	Female Terminal	Price Each			
							1	25	50	100
* 693-5003.0121.1	5003.0121.1	K	3	Rear Screw-on	538-03-12-1036	538-18-12-1222	10.36	8.93	8.35	7.97
* 693-5003.0221.1	5003.0221.1	K	6	Rear Screw-on	538-03-12-1036	538-18-12-1222	10.36	8.93	8.35	7.97
693-5003.1111.1	5003.1111.1	L	3	Front/Rear Screw-on	571-1-480700-0	538-02-08-1002	10.85	9.36	8.75	8.35
693-5003.1211.1	5003.1211.1	L	6	Front/Rear Screw-on	571-1-480700-0	538-02-08-1002	10.85	9.36	8.75	8.35
693-5003.1311.1	5003.1311.1	L	10	Front/Rear Screw-on	571-1-480700-0	538-02-08-1002	10.85	9.36	8.75	8.35
693-5003.1411.1	5003.1411.1	L	15	Front/Rear Screw-on	571-1-480700-0	538-02-08-1002	10.85	9.36	8.75	8.35
* 693-5003.1121.1	5003.1121.1	M	3	Rear Screw-on	571-1-480700-0	538-02-08-1002	10.85	9.36	8.75	8.35
* 693-5003.1321.1	5003.1321.1	M	10	Rear Screw-on	571-1-480700-0	538-02-08-1002	10.85	9.36	8.75	8.35
693-5003.0111.1	5003.0111.1	N	3	Front/Rear Screw-on	538-03-12-1036	538-18-12-1222	10.36	8.93	8.35	7.97
693-5003.0211.1	5003.0211.1	N	6	Front/Rear Screw-on	538-03-12-1036	538-18-12-1222	10.36	8.93	8.35	7.97
693-5003.0311.1	5003.0311.1	N	10	Front/Rear Screw-on	538-03-12-1036	538-18-12-1222	10.36	8.93	8.35	7.97
693-5003.0231.1	5003.0231.1	K	6	Front-Side	538-03-12-1036	538-18-12-1222	10.36	8.93	8.35	7.97
693-5003.0331.1	5003.0331.1	K	10	Front-Side	538-03-12-1036	538-18-12-1222	10.36	8.93	8.35	7.97
693-5003.1431.1	5003.1431.1	M	15	Front-Side	571-1-480700-0	538-02-08-1002	10.85	9.36	8.75	8.35



AC Power Connectors

Schurter