

CARLING TECHNOLOGIES Toggle Switches



2M1 SERIES, MINIATURE TOGGLE SWITCHES




** () = Momentary

For quantities greater than listed, call for quote.

MOUSER STOCK NO.		Fig.	Switch Current (125VAC)	Contact Form	Circuit**	Termination	Price Each		
Mfr.	Mfr. Part No.						1	25	50
691	—2M1-DP1-T1B1M1QE	A	5A	DPDT	ON-NONE-ON	Solder Lug	4.98	3.76	3.31
691	—2M1-DP1-T1B1M2QE	A	5A	DPDT	ON-NONE-ON	PCB	4.98	3.76	3.31
691	—2M1-SP1-T1B1M1QE	A	5A	SPST	ON-NONE-ON	Solder Lug	3.01	2.50	2.32
691	—2M1-SP1-T1B1M2QE	A	5A	SPST	ON-NONE-ON	PCB	3.01	2.50	2.32
691	—2M1-SP1-T2B4M6RE	A	5A	SPST	ON-NONE-ON	PC Mount, 90° horizontal	4.65	3.61	3.16
691	—2M1-SP3-T1B1M1QE	A	5A	SPST	ON-OFF-ON	Solder Lug	4.54	3.42	3.03
691	—2M1-SP3-T1B1M2QE	A	5A	SPST	ON-OFF-ON	PCB	4.54	3.42	3.03
691	—2M1-SP4-T1B1M1QE	A	5A	SPST	(ON)-OFF-(ON)	Solder Lug	4.89	3.68	3.26

DIMENSIONS: in.



CARLING POWER TOGGLE SWITCHES

Specifications:

- Actuator/Bushing Material: Brass/Nickel Plate
- 15/32" Threaded Bushing, 11/16" Toggle, 3/4" HP
- Combi Terminals Function as Both .250 QC Tabs and Solder Lug Terminal



* 1 HP ** () = Momentary

For quantities greater than listed, call for quote.

MOUSER STOCK NO.		Fig.	Current Rating	Contact Form	Circuit**	Termination	Price Each		
Mfr.	Mfr. Part No.						1	25	50
691	—110-73	B	6A	SPST	ON-NONE-OFF	Solder lug terminals	3.53	3.02	2.79
691	—110-S-73	B	6A	SPST	ON-NONE-OFF	Screw terminals	6.50	5.56	5.09
691	—111-16-73	B	6A	SPST	ON-NONE-OFF	Wire leads	6.50	5.56	4.88
691	—110-SPM-OFF	C	6A	SPST	OFF-(ON)	Screw terminals	16.75	12.54	11.18
691	—2BB62-73	D	6A	SPIT	ON-NONE-ON	Solder lug terminals	6.10	5.22	4.77
691	—2BK62-73	D	6A	IPST	ON-NONE-OFF	Solder lug terminals	8.86	6.69	6.14
691	—2BL62-73	E	6A	IPIT	ON-NONE-ON	Solder lug terminals	7.53	6.45	5.66
691	—DA100-BB-B	F	10A	SPST	ON-NONE-OFF	Solder Lug	2.22	2.07	1.69
691	—DA100-PB-B	F	10A	SPST	ON-NONE-OFF	Solder Lug	2.22	1.92	1.92
691	—DA105-PB-B	F	10A	SPST	ON-NONE-OFF	Wire Lead	3.24	3.06	3.06
691	—DC100-PB-B	C	10A	SPST	ON-OFF-ON	Solder Lug	3.39	2.73	2.73
691	—6FC58-73	G	10A	SPDT	ON-OFF-(ON)	Screw terminals	6.73	5.70	5.70
691	—2FA52-73	G	15A	SPST	ON-NONE-OFF	Combi terminals	5.02	4.29	3.77
691	—2FA53-73	G	15A	SPST	ON-NONE-OFF	Solder lug terminals	3.25	2.78	2.44
691	—2FA53-73/TABS	G	15A	SPST	ON-NONE-OFF	.250 QC Tabs	3.33	2.63	2.30
691	—2FA54-73	G	15A	SPST	ON-NONE-OFF	Screw terminals	3.50	2.98	2.75
691	—2FB53-73	G	15A	SPIT	ON-NONE-ON	Solder lug terminals	4.47	4.28	4.06
691	—2FB53-73/TABS	G	15A	SPIT	ON-NONE-ON	.250 QC Tabs	4.81	4.11	3.61
691	—2FB54-73	G	15A	SPIT	ON-NONE-ON	Screw terminals	5.66	4.84	4.25
691	—2FC53-73	G	15A	SPIT	ON-OFF-ON	Solder lug terminals	4.47	4.29	4.14
691	—2FC53-73/TABS	G	15A	SPIT	ON-OFF-ON	.250 QC Tabs	4.81	4.11	3.61
691	—2FC54-73	G	15A	SPIT	ON-OFF-ON	Screw terminals	6.12	5.23	4.77
691	—6GA5B-73	G	15A	SPDT	ON-NONE-(ON)	.250 QC Tabs	7.63	5.25	4.63
691	—6FA5473	H	15A	SPST	ON-NONE-OFF	-	7.73	7.33	6.96
691	—6FA5H-73	G	15A	SPST	(ON)-NONE-OFF	Combi terminals	7.70	7.35	6.65
691	—6FB5H-73	G	15A	SPIT	ON-NONE-(ON)	Combi terminals	7.99	6.05	5.54
691	—6FC54-73	G	15A	SPIT	(ON)-OFF-(ON)	Screw terminals	7.87	6.73	6.14
691	—6FC5H-73	G	15A	SPIT	(ON)-OFF-(ON)	Combi terminals	8.32	7.94	7.18
691	—6FC5Y-73	G	15A	SPIT	ON-OFF-(ON)	Combi terminals	8.69	7.94	7.18
691	—2FA5378/TABS	G	20A	SPIT	ON-NONE-OFF	Solder lug terminals	5.12	4.65	4.26
691	—6GG5B-73	G	15A	SPST	(ON)-OFF-(ON)	.250 QC Tabs	14.59	11.52	10.03
691	—2GG5173	H	20A	SPIT	ON-ON-OFF	PC terminal	6.85	6.49	6.16
691	—2GK50-73	H	15A	IPST	ON-NONE-OFF	Solder lug terminals	6.82	6.54	6.27
691	—2GK51-73	H	15A	IPST	ON-NONE-OFF	.250 QC Tabs	4.89	4.18	3.67
691	—2GK54-73	H	15A	IPST	ON-NONE-OFF	Solder lug terminals	10.22	9.99	9.87
691	—2GL50-73	H	15A	IPIT	ON-NONE-ON	Solder lug terminals	7.48	7.05	6.20
691	—2GL51-73	H	15A	IPIT	ON-NONE-ON	.250 QC Tabs	7.15	6.83	5.85
691	—2GL54-73	H	15A	IPIT	ON-NONE-ON	Screw terminals	9.09	7.77	7.11
691	—2GL57-73	H	15A	IPIT	ON-NONE-ON	Combi terminals	7.71	5.82	5.34
691	—2GM50-73	H	15A	IPIT	ON-OFF-ON	Solder lug terminals	8.06	7.36	6.31
691	—2GM51-73	H	15A	IPIT	ON-OFF-ON	.250 QC Tabs	5.39	4.61	4.05
691	—2GM54-73	H	15A	IPIT	ON-OFF-ON	Screw terminals	9.09	7.77	7.11
691	—6GL5B-73	I	15A	DPDT	ON-NONE-(ON)	.250 QC Tabs	15.42	11.11	9.81
691	—6GK5H-73	I	15A	IPST	(ON)-NONE-OFF	Combi terminals	12.90	9.67	9.14
691	—6GM5M73	I	15A	DPDT	ON-OFF-(ON)	.250 QC Tabs	13.41	12.39	11.72
691	—6GM5S-73	I	15A	DPDT	(ON)-OFF-(ON)	Screw terminals	17.62	12.70	11.21
691	—6GM5Y-73	I	15A	IPIT	(ON)-OFF-(ON)	Combi terminals	14.09	11.21	10.29
691	—HK251-73	J	15A	3PST	ON-NONE-OFF	.250 QC Tabs	10.59	9.50	8.50
691	—HL250-73	J	15A	3PIT	ON-NONE-ON	Solder lug terminals	14.14	11.06	10.45
691	—HL251-73	J	15A	3PIT	ON-NONE-ON	.250 QC Tabs	13.01	11.69	10.46
691	—HM250-73	J	15A	3PIT	ON-OFF-ON	Solder lug terminals	13.01	11.69	10.46
691	—HM251-73	J	15A	3PIT	ON-OFF-ON	.250 QC Tabs	13.00	9.82	9.00
691	—HM254-73	J	15A	3PIT	ON-OFF-ON	Screw terminals	16.99	12.83	11.71
691	—IL250-73	K	15A	4PIT	ON-NONE-ON	Solder lug terminals	24.00	16.35	14.35
*	691—IK284-73	L	16A	IPST	ON-NONE-OFF	Screw terminals	5.61	5.49	5.26
*	691—EK204-73	M	20A	IPST	ON-NONE-OFF	Screw terminals	13.10	9.90	9.08
691	—CA201-73	N	20A	SPST	ON-NONE-OFF	.250 QC Tabs	7.26	3.95	3.83
691	—LT1511610012	O	10A	SPIT	ON-NONE-OFF	.250 Tabs	10.56	10.00	9.50

Hardware				
691	—728-15907	-	Optional Lock Washer	.30 .20 .18

