


SONG CHUAN General Purpose Relays

RoHS Compliant This product is RoHS compliant.




DIMENSIONS: mm

GENERAL PURPOSE RELAYS

RoHS Compliant

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Song Chuan Part No.	Fig.	Contact Form	Contact Rating	Coil Voltage	Price Each			
						1	25	50	100
Miniature PCB Surge Relays									
893-875B1CCFS12VDC	875B-1CC-F-S-12VDC	A	SPDT	16A	12VDC	2.72	2.04	1.84	1.56
893-875B1CCFS24VDC	875B-1CC-F-S-24VDC	A	SPDT	16A	24VDC	2.72	2.04	1.84	1.56
High Inrush Miniature PCB Relays									
893-888H1AHFSIR12	888H-1AH-F-S-IR-12VDC	B	SPNO	17A	12VDC	3.11	2.86	2.57	2.32
893-888H1AHFSIR24V	888H-1AH-F-S-IR-24VDC	B	SPNO	17A	24VDC	3.49	2.62	2.35	2.08
Miniature Power Relays									
893-852W1AFC112VDC	852W-1A-F-C-1-12VDC	C	SPNO	25A	12VDC	3.16	2.82	2.50	2.38
893-852W1AFC124VDC	852W-1A-F-C-1-24VDC	C	SPNO	25A	24VDC	3.16	2.37	2.13	1.99
893-852WP1AFC12VDC	852WP-1A-F-C-1-12VDC	D	SPNO	25A	12VDC	3.16	2.37	2.13	1.91
893-852WP1AFC24VDC	852WP-1A-F-C-2-24VDC	D	SPNO	25A	24VDC	3.51	3.13	2.64	2.50
893-302WP1AHFC12VDC	302WP1-1AH-F-C-1-12VDC	E	SPNO	20A	12VDC	2.68	2.01	1.81	1.63
893-302WP1AHFC24VDC	302WP1-1AH-F-C-2-24VDC	E	SPNO	20A	24VDC	2.74	2.05	1.85	1.66
893-4012AHS12VDC	401-2AH-S-12VDC	F	DPNO	5A	12VDC	1.92	1.44	1.30	1.06
893-4012AHS24VDC	401-2AH-S-24VDC	F	DPNO	5A	24VDC	1.92	1.44	1.30	1.06
893-812H1CS12VDC	812H-1C-S-12VDC	G	SPDT	10A	12VDC	1.28	.96	.86	.71
893-812H1CS24VDC	812H-1C-S-24VDC	G	SPDT	10A	24VDC	1.28	.96	.86	.71
Flat Pack Miniature Relays									
893-8341AFS12VDC	834-1A-F-S-12VDC	H	SPNO	12A	12VDC	1.88	1.41	1.27	1.10
893-8341AFS24VDC	834-1A-F-S-24VDC	H	SPNO	24A	24VDC	1.95	1.46	1.31	1.14
Automotive Relays									
893-301CCS12VDC	301-1C-C-12VDC	I	SPDT	35A	12VDC	3.36	2.52	2.27	1.77
893-3031AHC12VDC	303-1AH-C-12VDC	J	SPNO	35A	12VDC	3.56	2.67	2.40	1.93
893-896H1CHC12VDC	896H-1CH-C-12VDC	K	SPDT	30A	12VDC	2.88	2.16	2.02	1.92
893-896HP1CHC12VDC	896HP-1CH-C-12VDC	K	SPDT	50A	12VDC	3.21	2.41	2.16	1.79
893-8971AHC12VDC	897-1AH-C-12VDC	L	SPNO	70A	12VDC	4.28	3.21	2.89	2.39
893-897P1AHC12VDC	897P-1AH-C-12VDC	L	SPNO	70A	12VDC	4.28	3.21	2.89	2.39
893-898H1CHC12V	898H-1CH-C-12VDC	M	SPDT	50A	12VDC	3.85	3.08	2.60	2.46
Miniature PCB Sugar Cube Relays									
893-833H1CS12VDC	833H-1C-S-12VDC	N	SPDT	10A	12VDC	1.35	1.01	.922	.773
893-833H1CS24VDC	833H-1C-S-24VDC	N	SPDT	10A	24VDC	1.00	.75	.68	.57
Heavy Duty General Purpose Relays									
893-832A1CFS12VDC	832A-1C-F-S-12VDC	O	SPDT	30A	12VDC	2.88	2.16	1.94	1.84
893-832A1CFS24VDC	832A-1C-F-S-24VDC	O	SPDT	30A	24VDC	2.88	2.16	1.94	1.84
893-832AW1CFC112VDC	832AW-1C-F-C-1-12VDC	O	SPDT	30A	12VDC	3.15	2.36	2.13	1.78
893-832AW1CFC124VDC	832AW-1C-F-C-1-24VDC	O	SPDT	30A	24VDC	3.00	2.25	2.03	1.70
893-832AWP1CS12VDC	832AWP-1C-S-12VDC	O	SPDT	30A	12VDC	4.80	3.60	3.24	2.72
893-832AWP1CS24VDC	832AWP-1C-S-24VDC	O	SPDT	30A	24VDC	3.24	2.43	2.19	1.84
General Purpose Power Relays									
893-703XB12VDC	703XB-12VDC	P	DPDT	10A	12VDC	10.72	8.04	7.24	6.31
893-703XB24VDC	703XB-24VDC	P	DPDT	10A	24VDC	10.72	8.04	7.24	6.31
893-703XB120VAC	703XB-120VAC	P	DPDT	10A	120VAC	10.72	8.04	7.24	6.31
893-703XB240VAC	703XB-240VAC	P	DPDT	10A	240VAC	11.56	8.67	7.80	6.31
893-703XC12VDC	703XC-12VDC	P	3PDT	10A	12VDC	12.40	9.30	8.37	7.45
893-703XC24VDC	703XC-24VDC	P	3PDT	10A	24VDC	12.40	9.30	8.37	7.45
893-703XC120VAC	703XC-120VAC	P	3PDT	10A	120VAC	12.40	9.30	8.37	7.45
893-703XC240VAC	703XC-240VAC	P	3PDT	10A	240VAC	13.20	9.90	8.91	7.45
893-731DPDTC12VDC	731-DPDT-C-12VDC	Q	DPDT	10A	12VDC	12.26	9.19	8.27	6.83
893-731DPDTC24VDC	731-DPDT-C-24VDC	Q	DPDT	10A	24VDC	17.28	12.96	11.66	9.63
893-731DPDTC120VAC	731-DPDT-C-120VAC	Q	DPDT	10A	120VAC	11.32	8.49	7.64	6.31
893-731DPDTC240VAC	731-DPDT-C-240VAC	Q	DPDT	10A	240VAC	18.44	13.83	12.44	9.59
893-731TPDTC12VDC	731-TPDT-C-12VDC	Q	3PDT	10A	12VDC	18.28	13.71	12.33	10.81
893-731TPDTC24VDC	731-TPDT-C-24VDC	Q	3PDT	10A	24VDC	18.28	13.71	12.33	10.81
893-731TPDTC120VAC	731-TPDT-C-120VAC	Q	3PDT	10A	120VAC	18.28	13.71	12.33	10.81
893-731TPDTC240VAC	731-TPDT-C-240VAC	Q	3PDT	10A	240VAC	18.44	13.83	12.43	10.25
893-SCLDPDT12VDC	SCL-DPDT-12VDC	R	DPDT	12A	12VDC	6.99	6.41	5.83	5.25
893-SCLDPDT24VDC	SCL-DPDT-24VDC	R	DPDT	12A	24VDC	6.32	5.83	5.25	4.86
893-SCLDPDT24VAC	SCL-DPDT-24VAC	R	DPDT	12A	24VAC	6.32	5.83	5.25	4.66
893-SCLDPDT120VAC	SCL-DPDT-120VAC	R	DPDT	12A	120VAC	6.60	4.95	4.46	3.55
893-SCLBWDPDT12VDC	SCLB-W-DPDT-C-12VDC	R	DPDT	5A	12VDC	5.16	3.87	3.48	3.01
893-SCLBWDPDT24VDC	SCLB-W-DPDT-C-24VDC	R	DPDT	5A	24VDC	5.16	3.87	3.48	3.01
893-SCLBWDPDT120VAC	SCLB-W-DPDT-C-120VAC	R	DPDT	5A	120VAC	5.20	3.90	3.51	3.01
893-SCLDW4PDT12VDC	SCLD-WB-4PDT-C-12VDC	R	4PDT	5A	12VDC	6.64	4.98	4.48	3.72
893-SCLDW4PDT24VDC	SCLD-WB-4PDT-C-24VDC	R	4PDT	5A	24VDC	8.32	6.24	5.61	4.66
893-SCLDW4PDT120VAC	SCLD-WB-4PDT-C-120VAC	R	4PDT	5A	120VAC	6.88	5.16	4.64	3.72



General Purpose Relays Song Chuan