

TE High Performance Relays



HIGH CURRENT RELAY (HCR) 200

PRODUCT **NEW**

For quantities greater than listed, call for quote.


MOUSER STOCK NO.	TE Part No.	Fig.	Coil Voltage (VDC)	Current Rating (A)	Coil Res. (Ω)	Contact Arrangement	Enclosure	Price Each	
								1	5
655-V23230D2001B200	1414995-0	A	12	175	43	1 Form B, 1NC	IP64	75.11	65.41



1/5 SIZE LOW SIGNAL RELAYS

For quantities greater than listed, call for quote.


MOUSER STOCK NO.	TE Part No.	Fig.	Input Voltage (VDC)	Current Rating (A)	Coil Res. (Ω)	Contact Arrangement	Mounting Type	Approved Standards	Price Each	
									1	5
655-3SBC2002A2	1-1617073-4	B	26.5	2	1350	2 Form C, DPDT, 2 C/O	PC	P	170.09	164.57



1/2 SIZE CRYSTAL CAN RELAYS

For quantities greater than listed, call for quote.


MOUSER STOCK NO.	TE Part No.	Fig.	Input Voltage (VDC)	Current Rating (A)	Coil Res. (Ω)	Contact Arrangement	Mounting Type	Approved Standards	Price Each	
									1	5
655-HFW1131K04M	3-1617029-3	C	26.5	2	700	2 Form C, DPDT, 2 C/O	Chassis	-	76.37	73.89
655-HFW1201G01M	2-1617030-7	C	12	2	900	2 Form C, DPDT, 2 C/O	PC	M	78.66	76.10
655-HFW1201K45	2-1617031-0	C	26.5	2	700	2 Form C, DPDT, 2 C/O	PC	L	78.66	76.10
655-HFW1201K45M	2-1617031-1	C	26.5	2	700	2 Form C, DPDT, 2 C/O	PC	M	76.37	73.89
655-HFW1201K45P	2-1617031-2	C	26.5	2	700	2 Form C, DPDT, 2 C/O	PC	P	84.88	82.14
655-HFW1201K46	2-1617031-3	C	26.5	2	700	2 Form C, DPDT, 2 C/O	PC	L	78.66	76.10
655-HFW1201K46M	2-1617031-4	C	26.5	2	700	2 Form C, DPDT, 2 C/O	PC	M	78.66	76.10
655-HFW1230K06	2-1617033-9	C	26.5	2	700	2 Form C, DPDT, 2 C/O	Chassis	L	76.37	73.89
655-HFW5A1201K00	1617037-9	C	26.5	5	700	2 Form C, DPDT, 2 C/O	PC	-	164.98	159.63



FULL SIZE CRYSTAL CAN RELAYS

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	TE Part No.	Fig.	Input Voltage (VDC)	Current Rating (A)	Coil Res. (Ω)	Contact Arrangement	Mounting Type	Price Each	
								1	5
655-B07D634BC2-0051	2-1617004-8	D	26.5	10	300	2 Form C, DPDT, 2 C/O	Socket	175.90	170.19
655-B07D692BZ2-0011	3-1617004-2	D	26.5	10	300	2 Form C, DPDT, 2 C/O	Chassis	175.90	170.19
655-B07D932BC2-0348	4-1617004-0	D	26.5	10	300	2 Form C, DPDT, 2 C/O	Panel	175.90	170.19



FCA STANDARD MID-RANGE RELAYS

* With coil suppression diode

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	TE Part No.	Fig.	Coil Voltage (VDC)	Current Rating (A)	Terminal Configuration	Contact Arrangement	Mounting Type	Price Each	
								1	5
* 655-FCA-210-1027M	2-1617749-5	D	28	10	Solder Pins	2 Form C, DPDT, 2 C/O	Side	146.69	141.92
* 655-FCA-410-1622M	2-1617754-1	D	28	10	Socket Pins	4 Form C, 4PDT, 4 C/O	Bottom	169.87	164.35



FCB COMPACT MID-RANGE RELAYS

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	TE Part No.	Fig.	Coil Voltage (VDC)	Current Rating (A)	Terminal Configuration	Contact Arrangement	Mounting Type	Price Each	
								1	5
655-FCB-205-0224M	5-1617758-0	D	28	5	Socket Pins	2 Form C, DPDT, 2 C/O	Bottom	149.78	139.09
655-FCB-205-0228M	5-1617758-4	D	28	5	Socket Pins	2 Form C, DPDT, 2 C/O	Track	156.67	151.58
655-FCB-405-0622M	8-1617760-3	D	28	5	Socket Pins	4 Form C, 4PDT, 4 C/O	Bottom	174.96	169.28



TO-5 LOW SIGNAL RELAY

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	TE Part No.	Fig.	Input Voltage (VDC)	Current Rating (A)	Coil Res. (Ω)	Contact Arrangement	Mounting Type	Approved Standards	Price Each	
									1	5
655-JMAC-26XP	1-1617121-1	E	26.5	1	1560	2 Form C, DPDT, 2 C/O	PC	P	94.29	91.23

HIGH PERFORMANCE CONTACTORS

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	TE Part No.	Fig.	Coil Voltage (VDC)	Current Rating (A)	Contact Arrangement	Mounting Type	Price Each	
							1	5
655-LEV100A5ANG	9-1618389-8	F	24	100	1 Form X, SPST-NO-DM	Bottom	110.56	100.83
655-LEV200A4ANA	1618387-3	F	12	500	1 Form A, SPST-NO	Bottom	120.49	109.89
655-LEV200A5ANA	7-1618387-1	F	24	500	1 Form X, SPST-NO-DM	Bottom	120.49	109.89
655-EV200HAANA	1-1618002-8	F	9-36	500	1 Form A, SPST-NO, 1 N/O	Panel	214.68	193.21

General Purpose Relays TE Connectivity