

NEW AGE Plastic Enclosures

NEW AGE ENCLOSURES

ASA INDUSTRIAL UTILITY ENCLOSURES

RoHS Compliant This product is RoHS compliant.




MOUSER STOCK NO.	New Age Enclosures Part No.	Fig.	Description	Dimensions: in.	Color	Size/ Capacity	Price Each			
							1	10	25	100
789-S3L-452715-SS	S3L-452715-SS	A	Standard base and cover	4.53 x 2.72 x 1.43	Black	-	18.06	14.80	13.89	13.09
789-S3L-452715-SW	S3L-452715-SW	A	Standard with wall mount	4.53 x 2.72 x 1.25	Black	-	18.06	14.80	13.89	13.09
789-S3L-452715-BS	S3L-452715-BS	A	Battery with standard base	4.53 x 2.72 x 1.60	Black	1 9V, 2 AA, 2 AAA	19.96	16.36	15.35	14.46
789-S3L-452715-BW	S3L-452715-BW	A	Battery with wallmount	4.53 x 2.79 x 1.43	Black	1 9V, 2 AA, 2 AAA	19.96	16.36	15.35	14.46
789-S6L-452715-SS	S6L-452715-SS	A	Standard base and cover	4.53 x 2.72 x 1.43	Gray	-	18.06	14.80	13.89	13.09
789-S6L-452715-SW	S6L-452715-SW	A	Standard with wall mount	4.53 x 2.72 x 1.25	Gray	-	18.06	14.80	13.89	13.09
789-S6L-452715-BS	S6L-452715-BS	A	Battery with standard base	4.53 x 2.72 x 1.60	Gray	1 9V, 2 AA, 2 AAA	19.96	16.36	15.35	14.46
789-S6L-452715-BW	S6L-452715-BW	A	Battery and wallmount	4.53 x 2.79 x 1.43	Gray	1 9V, 2 AA, 2 AAA	19.96	16.36	15.35	14.46
789-S-452715-OR	S6L-452715-OR	-	O-Ring kit 2 pcs	-	Black	-	2.82	2.31	2.17	2.04




ABS PLASTIC SCREW TOGETHER KEY FOB ENCLOSURES

MOUSER STOCK NO.	New Age Enclosures Part No.	Fig.	Dimensions: in.	Color	Price Each			
					1	10	25	100
789-S1A-251605	S1A-251605	B	2.5 x 1.6 x 0.5	White	3.44	2.82	2.62	2.53
789-S3A-251605	S3A-251605	B	2.5 x 1.6 x 0.5	Black	2.92	2.39	2.23	2.15




ABS PLASTIC SCREW TOGETHER UTILITY ENCLOSURES

MOUSER STOCK NO.	New Age Enclosures Part No.	Fig.	Dimensions: in.	Color	Price Each			
					1	10	25	100
Small								
789-S1A-272008	S1A-272008	C	2.75 x 2.0 x 0.8	White	3.61	2.96	2.76	2.64
789-S3A-272008	S3A-272008	C	2.75 x 2.0 x 0.8	Black	3.61	2.96	2.76	2.64
Medium								
789-S1A-352510	S1A-352510	C	3.5 x 2.5 x 1.0	White	4.40	3.61	3.37	3.23
789-S3A-352510	S3A-352510	C	3.5 x 2.5 x 1.0	Black	4.40	3.61	3.37	3.23
Large								
789-S1A-453212	S1A-453212	C	4.5 x 3.25 x 1.25	White	5.30	4.43	4.21	4.00
789-S3A-453212	S3A-453212	C	4.5 x 3.25 x 1.25	Black	5.30	4.43	4.21	4.00



ABS PLASTIC PRESS FIT VENTED UTILITY ENCLOSURES

MOUSER STOCK NO.	New Age Enclosures Part No.	Fig.	Dimensions: in.	Color	Price Each			
					1	10	25	100
789-P1A-251714	P1A-251714	D	2.5 x 1.7 x 1.4	White	2.90	2.38	2.23	2.10
789-P3A-251714	P3A-251714	D	2.5 x 1.7 x 1.4	Black	2.90	2.38	2.23	2.10




ABS PLASTIC SCREW TOGETHER OUTDOOR UTILITY ENCLOSURES

MOUSER STOCK NO.	New Age Enclosures Part No.	Fig.	Dimensions: in.	Color	Price Each			
					1	10	25	100
789-S3A-523322	S3L-523322	E	5.18 x 3.10 x 1.17	Black	8.50	6.97	6.50	6.25
789-S3A-523322WP	S3L-523322WP	-	5.18 x 3.10 x 1.17 Wall Plate	Black	3.62	2.97	2.79	2.62
789-SE-523322OR	S-523322OR	-	O-Ring, Use For Outdoor Utility	Natural	2.08	1.71	1.59	1.53




ABS PLASTIC SCREW TOGETHER HANDHELD ENCLOSURES

MOUSER STOCK NO.	New Age Enclosures Part No.	Fig.	Dimensions: in.	Color	Price Each			
					1	10	25	100
Medium								
789-S3A-442710	S3A-442710	F	4.4 x 2.7 x 1.0	Black	6.90	5.66	5.28	5.07
Large								
789-S3A-784114	S3A-784114	G	7.8 x 4.1 x 1.4	Black	6.96	5.71	5.29	5.12
Accessories								
789-209	209	-	Single, "AA" Snap-On Battery Clip	Steel	.22	.18	.17	.16
789-210	210	-	Double, "AA" Snap-On Battery Clip	Steel	.33	.31	.29	.27




ABS PLASTIC PRESS TOGETHER ELECTRONIC HOUSING ENCLOSURES

MOUSER STOCK NO.	New Age Enclosures Part No.	Fig.	Dimensions: in.	Color	Price Each			
					1	10	25	100
789-P1A-301910	P1A-301910	H	3.0 x 1.9 x 1.0	White	3.35	2.75	2.56	2.46
789-P3A-301910	P3A-301910	H	3.0 x 1.9 x 1.0	Black	3.35	2.75	2.56	2.46




ABS PLASTIC SCREW TOGETHER WIRELESS WALL MOUNT ENCLOSURES

MOUSER STOCK NO.	New Age Enclosures Part No.	Fig.	Dimensions: in.	Color	Price Each			
					1	10	25	100
789-S1A-442710-WE	S1A-442710-WE	I	4.4 x 2.7 x 1.0 Wall Mount	White	7.40	6.07	5.66	5.44
789-S1A-442710-WP	S1A-442710-WP	-	5.35 x 3.10 x 1.17 Wall Plate	White	2.56	2.10	1.96	1.88
789-S3A-442710-WE	S3A-442710-WE	I	4.4 x 2.7 x 1.0 Wall Mount	Black	7.40	6.07	5.66	5.44
789-S3A-442710-WP	S3A-442710-WP	-	5.35 x 3.10 x 1.17 Wall Plate	Black	2.56	2.10	1.96	1.88
789-S1A-434313S	S1A-434313S	I	4.28 x 4.28 x 1.31	White	4.23	3.47	3.25	3.06
789-S3A-434313S	S3A-434313S	I	4.284 x 4.284 x 1.31	Black	4.23	3.47	3.25	3.06
789-S1A-434313SW	S1A-434313SW	I	4.284 x 4.284 x 1.31	White	4.23	3.47	3.25	3.06
789-S3A-434313SW	S3A-434313SW	I	4.284 x 4.284 x 1.31	Black	4.23	3.47	3.25	3.06
789-S1A-434313F	S1A-434313F	I	4.28 x 4.28 x 1.31	White	4.23	3.47	3.25	3.06
789-S3A-434313F	S3A-434313F	I	4.2854 x 4.284 x 1.31	Black	4.23	3.47	3.25	3.06
789-S1A-434313FW	S1A-434313FW	I	4.28 x 4.28 x 1.31	White	4.23	3.47	3.25	3.06
789-S3A-434313FW	S3A-434313FW	I	4.284 x 4.284 x 1.31	Black	4.23	3.47	3.25	3.06
789-S1A-312208	S1A-312208	I	3.09 x 2.25 x .84	White	2.41	1.97	1.85	1.74



ABS PLASTIC 9 VOLT HAND HELD ENCLOSURES

MOUSER STOCK NO.	New Age Enclosures Part No.	Fig.	Dimensions: in.	Color	Price Each			
					1	10	25	100
789-S1A-382410B	S1A-382410B	J	3.8 x 2.4 x 1.0 w/o Battery Clip	White	5.75	4.72	4.40	4.22
789-S3A-382410B	S3A-382410B	J	3.8 x 2.4 x 1.0 w/o Battery Clip	Black	5.75	4.72	4.40	4.22
789-S1A-382410S	S1A-382410S	J	3.8 x 2.4 x 1.0 w/o Battery Clip	White	4.83	3.96	3.70	3.54
789-S3A-382410S	S3A-382410S	J	3.8 x 2.4 x 1.0 w/o Battery Clip	Black	4.83	3.96	3.70	3.54



New Age Enclosures

Plastic Boxes