| DATE | DESCRIPTION | REV. |
|---|---|---|
| | | |

Notes:

Front Shell: Brass, Nickel Plate.
Rear Shell: Steel, Nickel Plate.

Insulator: Mat'l: Thermoplastic
UL 94V-0

Contacts: Mat'l: Phosphor Bronze
Finish: Gold Plate over
Nickel Plate on
Contact Area.
Tin Plate over
Nickel Plate
on Solder Tail.

Electrical Specifications
Rated Voltage:
30V AC (rms)

Contact Current Rating:
1A Max.

Contact Resistance:
30 milliohms Max.

Dielectric Withstanding:
500V AC

Operating Temperature:
-20°C to 85°C

PACKAGING DESCRIPTION:
Packed in 500 Pieces per lots.
50 Pieces per Tray, 10 Trays per lot.







**KEYSTONE ELECTRONICS CORP.**
www.keyelco.com • NEW HYDE PARK, NY 11040 • Tel (516) 328-7500

| | | | |
|---|---|---|---|
| PART NAME | USB B-TYPE HORIZONTAL SMT SOCKET | | |
| MATERIAL | AS NOTED | | |
| FINISH | AS NOTED | DRN BY BOONE | DATE 5.30.06 |
| | | APP'D RH | SCALE 3X |
| TOLERANCES INCH [MM] DECIMAL ± .010 [± 0.25] ANGULAR ± 1° UNLESS OTHERWISE SPECIFIED | CODE C | DWG NO. 933 | |

THIS DOCUMENT IS THE PROPERTY OF KEYSTONE ELECTRONICS CORP. AND SHALL NOT BE REPRODUCED, DISTRIBUTED OR USED AS A BASIS FOR MANUFACTURE WITHOUT PRIOR WRITTEN PERMISSION FROM KEYSTONE ELECTRONICS CORP.