1. SPECIFICATION

AC-1001N-RP5

ITEM		UNITS	SPECIFICATIONS	CONDITIONS
01	Rated Voltage	V	1.5	
02	Operating Voltage	V	1 ~ 3	
03	Consumption Current	mA (Max)	Mean： 80 Peak： 240	Applying rated voltage, rated frequency Square wave, 1/2 duty subject to standard state.
04	Direct Current Resistance	Ω	5.5 ± 1.0	
05	Sound pressure level (Distance at 10cm)	dBA (Min)	85	Applying rated voltage, rated frequency Square wave, 1/2 duty subject to standard state.
06	Rated Frequency	Hz	2731	

AIC

REV NO.	REVISION NOTE	APPROVAL	DATE





RoHS

TITLE: ELECTRO MAGNETIC BUZZER		DRAWN: Zack 2013/12/17	SCALE: 4:1	SHEET: 1 of 1
PART NO. AC−1001N−RP5	1	DESIGNED: R&D OF AAT	UNITS: mm	
DWG NO. UGCM0901B2PD	REV	CHECKED:	TOLERANCE ± 0.5	
		APPROVAL:	UNLESS OTHERWISE SPECIFIED: ONE PLACE DECIMAL ± *** TWO PLACE DECIMAL ± *** THREE PLACE DECIMAL ± ***	
		MATERIAL: NORYL		

ADVANCED ACOUSTIC TECHNOLOGY CORPORATION

For more information, please contact AATC.

AATC