Catalog No. T2111

Titanium-Coated High-Leverage Professional Shears, 10-Inch

The Titanium-Coated High-Leverage Professional Shears cut a versatile range of materials such as thick leather, flooring, roofing, and thin sheet metal. The ambidextrous grips provide maximum comfort and allow for a wide range of use for both left and right-handed users. The titanium-coated stainless steel blades allow easier cutting of heavy-duty materials.

Specifications

Type:	Shear	**Special Features:**	Titanium Coated Blades
Application:	Cuts Thick Leather, Flooring, Roofing, Thin Sheet Metal	**Material:**	Stainless Steel
Blade Curvature:	Straight	**Blade Edge:**	Serrated
Blade Length (Inch):	3.75	**Blade Length (cm):**	9.5
Blade Tip:	Standard	**Blade Finish:**	Stainless Steel With Titanium Coating
Handed:	Ambidextrous	**Handle Color:**	Orange/Black
Handle Material:	Plastic	**Handle Orientation:**	Straight
Handle Length (Inch):	6	**Handle Length (cm):**	15.2
Cutting Length (Inch):	3.75	**Cutting Length (cm):**	9.5
Handled:	Ambidextrous	**Handle Type:**	Plastic
Tension Adjustment:	Yes	**Inside Ring Size (Inch):**	0.91
Inside Ring Size (cm):	2.3	**Overall Length (Inch):**	9.8
Overall Length (cm):	24.9	**Overall Height (Inch):**	3.6
Overall Height (cm):	9.1	**Overall Width (Inch):**	0.8
Overall Width (cm):	2	**Weight (oz):**	11
Weight (g):	312		