

# X300 Series

## Compact Cellular IoT Gateway Solution



Ideal for mission-critical applications, the new X300 Cellular Compact IoT Gateway Solution combines Lantronix's IoT gateway hardware with a premium services subscription, including centralized device management, cellular data, enhanced security, and expert technical support in an all-in-one package.

The X300 Series offers extensive IoT communication with LTE M or Cat-1 cellular, Wi-Fi, Bluetooth/BLE, Ethernet, and serial interface in a small, industrial-grade form factor. The X300's combined offering gives you everything you need to guarantee your project's success.

- **ConsoleFlow™** Premium cloud-based device management and analytics software platform
- **Connectivity Services** embedded SIM card with scalable cellular data plans
- **LEVEL Technical Services** providing technical experts and limited lifetime hardware warranty

### Industrial Grade, Compact Form Factor

The Lantronix X300 Series gateway is a compact (79 x 79 mm) IoT gateway with multiple hardware interfaces available such as a multi-mode Serial, an Ethernet, cellular, Wi-Fi and Bluetooth/BLE. The gateway is designed for complex deployments in harsh environments, even where space is limited.

### Built-in Security Framework with Lantronix InfiniShield™

The highest level of security for mission-critical applications is key to preventing cyber security threats. InfiniShield™ Security provides a comprehensive security suite, including a secure element chip, enables secure boot, access, and data communications, preventing unauthorized access.

### Process and Customize at the Edge

With the ePACK software suite, based on Linux framework, the X300 IoT gateway provides a user-friendly environment to develop your application and leverage the Linux development community applications.

### BLE Sensors Accessory to Collect More Critical Data

Read temperature, humidity, sense motion or get ID location via a complete range of integrated BLE sensors.

### Perfect For:



Digital Signage



Industry 4.0




Remote Asset Management



BLE Gateway

### X300 Series Highlights

- Compact industrial-grade design
- Multiple hardware interfaces
- Latest Cyber Security protection
- Premium ConsoleFlow Device Management
- Integrated Lantronix Connectivity Services
- Expert Technical Support
- Limited Lifetime Warranty
- Advanced hardware replacement



### Lantronix Software Services

**ConsoleFlow™** - secure cloud platform to manage remote IoT gateways through a single pane of glass. [lantronix.com/consoleflow](http://lantronix.com/consoleflow)

**Connectivity Services** - Global cellular data plans and VPN security with an easy-to-use cloud platform to manage your SIMs and services. [lantronix.com/connectivity-services](http://lantronix.com/connectivity-services)

**LEVEL 2 Technical Services** - providing fast response, configuration assistance, software updates and advanced hardware replacement. [lantronix.com/level](http://lantronix.com/level)

## Hardware

### Cellular

- LTE Cat M1 - X303 with 2G fallback mode
- LTE Cat1 - X304 with 3G or 2G fallback mode options

### Wi-Fi & Bluetooth Operation

- Wi-Fi 5 and Bluetooth/BLE 5.0; via one (X303) or two (X300, X304) RP-SMA antenna connector

### Ethernet

- One LAN port; 10/100BASE-T; via a RJ-45 header fitted with two LEDs

### Serial Communication

- RS-232 6-signal (Rx, Tx, RTS, CTS, either DSR or DCD, DTR) implementation; via an RJ-45 header
- RS-485 half or full duplex, via RJ-45 header
- Switchable by software

### SIM

- Lantronix Connectivity Services embedded MFF SIM; auxiliary mini-SIM holder

### Location Services

- Qualcomm® iZat™ gen. 8C gps One; via a dedicated SMA antenna connector (X304 only)

### Memory & Data Storage Security Chip

#### RAM

- DDR2 SDRAM 128MB

#### SPI Flash Memory

- 8MB

#### User Data Storage

- Internal: via the parallel 256MB NAND Flash memory
- External: via a user-accessible microSD card (not provided)

### Physical Description

- Brushed aluminum alloy
- Size: 79 x 79 x 23.5 mm without connectors
- Weight: approximately 150 grams
- Operating Status LEDs: Seven as green for (i) POWER; blue for (ii) SIM; (iii) Wi-Fi; amber for (iv) Activity; (v) Network; (vi) Signal; red for (vii) ALERT

### Temperature & Humidity Ranges

- Operating: -30°C ~ +70°C; up to 95% RH
- Storage: -40°C ~ +85°C; up to 95% RH

### CPU

- ARM926EJ-S-based CPU running at 600 MHz
- Built-in 32 KB instruction cache and 32 KB data cache

### Power

- Input voltage: 9 ~ 30 V DC
- 3-pin Nano-Fit™ header
- Digital Input (Ignition): One (1) digital input, on the second pin of the 3-pin header
- Input: 0 ~ 2.5 V DC => ZERO; 3 ~ 50 V DC => ONE

## Software Suite

### Administration & Network Protocols

- Web-based user interface, setup wizard, console log viewer, save / load configuration, NTP, SMS / OTA remote configuration, TR-069-capable, and Lantronix Provisioning Manager

### Redundancy

- Ethernet, Cellular, Wi-Fi – configurable as failover or load balancing

### Resilience

- Network connectivity watchdog (configurable), internal application watchdog

### Wi-Fi

- InfiniShield™ Security Client or Access point (approx. 12 users), WPA, WPA-PSK / WPA2-PSK / WPA3-PSK. Enterprise Security (WPA2-Enterprise/ WPA3-Enterprise). WPA3 not available for Access point mode.

### Device Management Services

- Lantronix ConsoleFlow™ platform – 1 year of Premium subscription included

### Performance & Fault Management

- Real time processor load and interface (WAN / LAN / Wi-Fi), traffic analysis, ICMP, trace-route, NS lookup

### Routing

- DHCP, static routing, port forwarding, traffic routing, static / dynamic DNS, DNS proxy, NAT, STP

### VPN & Tunneling Protocols

- Wireguard, PPTP client, L2TP, OpenVPN client / server / passthrough, GRE, IPsec up to 4 channels

### Essential IoT Applications

- Serial and Bluetooth SPP to Network tunnels. Packages are available as IPKs for installation.
- Add your own IoT edge applications with the SDK and ImageBuilder.

### Security

- Secure boot, zone-based firewall, VLAN, DMZ, HTTPS local and remote connection, SIM PIN

### Essential Accessories

Visit [lantronix.com/x300](http://lantronix.com/x300) for a full listing of accessories and ordering information.

#### Power Cord

- Power Cord - KDC32 or KDC33 (with one more stripped wire for Ignition)
- Power supply - ACC-520-0165-00, wall cube, 12 V DC 12W, 4 AC plugs, Level 6, with PSE

#### Din Rail Clip

- BR250 single mount 4½ U width; or doubling as 4-hole mounting brackets
- BR475, dual mount 4¾ U / 1¾ U widths

#### Remote (3 M), Adhesive, Antenna

- A31M0, or ACC-A31H1, LTE: X303
- A32M0, '2-in-1' LTE + LTE: X304, should its GNSS operation be ignored
- A33M0, '3-in-1' LTE + LTE + GNSS: X304

#### Wi-Fi Antenna(s)

- A21H0, L-shaped, hinged: X303
- Pair of A21H0, L-shaped, hinged: X300, X304

## Ordering Information

Part Number	Description
X300F202S	Wireless gateway
X303F202S	Worldwide - LTE-M gateway
X304G00AS	USA/Canada - LTE Cat 1 gateway
X304G000S	Latin America - LTE Cat 1 gateway
X304G002S	EMEA/APAC - LTE Cat 1 gateway
X304G007S	Japan/South Korea - LTE Cat 1 gateway
X304G00CS	China/India/Thailand/Indonesia - LTE Cat 1 gateway

## All Bundles Include

ConsoleFlow Premium	Premium ConsoleFlow™ device management platform for managing deployments of one to thousands of sites, including quick-and-easy access to assets and the ability to easily push new configurations and firmware upgrades.
LEVEL 2 Services	LEVEL 2 Technical Services providing fast response, configuration assistance, software updates and advanced hardware replacement.
Connectivity Services	Convenient and scalable cellular data plans - Contact your Rep to select the data plan (Not applicable for X300F202S)
A31M0 Only X303	Single LTE antenna, adhesive remote antenna with 3000MM RG174 cable, SMA male
A33M0 Only X304	Three-in-one LTE antenna, (2) LTE+GPS/glonass/bd antenna, 3000mm rg174 cable with (3) SMA male, adhesive mount.
A21H0	2.4/5.8GHZ Dipole Antenna for ISM & WLAN, RP-SMA(M)HINGED.
ACC-520-0165-00	Power supply, wall cube, 12VDC 12W, 4 AC plugs, Level 6, with PSE, 1X3.0MM latched conn output

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Lantronix](#):

[X303F202S](#) [X304G00AS](#) [X300F202S](#) [X304G000S](#) [X304G002S](#) [X304G007S](#)