



ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	B	ECO-14311	03/04/2025	TDUFRENE	DGUST



F

F



2X MOLDING,  
40P PCV BLACK

C19 LA FEMALE PLUG  
BRASS  
TERMINALS



NOTES:

1. CABLE:  
SJT 12AWG 3C 105°C 300V VW-1 JACKET: PVC, BLACK  
MARKING (NO.682): (UL) E135710-F5 SJT 3X12AWG 105°C 300V VW-1  
C(UL) SJT 3X3.31MM2(12AWG) 105°C 300V FT2
2. ELECTRICAL CHARACTERISTICS:  
DIELECTRIC VOLTAGE WITHSTAND TEST: 1500V / 1 SEC  
CONDUCTOR RESISTANCE  $\leq$  5.69Ω/1000M AT 20°C  
VOLTAGE RATING: AC 300V AT 20°C.
3. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION).

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED  
LEADING DIMENSIONS ARE INCHES  
DIMENSIONS IN [ ] ARE MILLIMETERS

TOLERANCES:  
X =  $\pm .2$  [5]  
XX =  $\pm .02$  [0.5]  
XXX =  $\pm .005$  [0.13]

FRACTIONS  
 $\pm 1/32$   
ANGLES  $\pm 1^\circ$

CABLE LENGTH TOLERANCES:  
 $\leq 12$  [305] =  $\pm 1$  [25] / -  
 $> 12$  [305]  $\leq 60$  [1524] =  $\pm 2$  [51] / -  
 $> 60$  [1524]  $\leq 120$  [3048] =  $\pm 4$  [102] / -  
 $> 120$  [3048]  $\leq 300$  [7620] =  $\pm 6$  [152] / -  
 $> 300$  [7620] =  $\pm 5\%$  / -

ALL DIMENSIONS ARE FOR REFERENCE ONLY  
AND SUBJECT TO CHANGE WITHOUT NOTICE  
UN-DIMENSIONED/NON-CRITICAL FEATURES  
MAY VARY IN SIZE AND LOCATION  
COLORS MAY VARY

**L-com**  
an INFINITE brand

Website: [www.L-com.com](http://www.L-com.com)  
Phone: 1.800.341.5266 | 1.978.682.6936

INTERPRET ALL DIMENSIONS AND  
TOLERANCES PER ASME Y14.5

SCALE  
NONE

SHEET  
1 OF 1

DESCRIPTION  
N5-15-C19 LA POWER CORD, 15 AMP

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	43321	TDUFRENE	PCS02L2-BLK	B

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[L-Com](#):

[PCS02L2-BLK-15F](#) [PCS02L2-BLK-6F](#) [PCS02L2-BLK-10F](#)