

Specification Sheet

Part Number: MB4A10A2C2


For use with HellermannTyton T18 - T50 cable ties to provide stability when securing bundles.

4-way opening allows cable ties to be installed parallel or perpendicular to bundles.

The rubber-based adhesive is an economical choice ideal for indoor applications, with a static load weight of 1.1 lb.

Two predrilled holes extend mounting options and solutions.

Extended adhesive liner is easy to remove quickly.



Acrylic Adhesive Cable Tie Mount, 1.12 x 1.12", Use With T18-T50 Cable Tie, PA66, White, 100/pkg

Article Number	151-28420
----------------	-----------

Type	MB4A
------	------

Color	White (WH)
-------	------------

Quantity Per	pack
--------------	------

Product Description	MB4A adhesive mounts are for use with HellermannTyton T18 - T50 Series cable ties to provide stability when securing bundles. The rubber adhesive-backed mounts can be used to secure a bundle and have two predrilled holes to extend mounting options.
---------------------	--

Short Description	Acrylic Adhesive Cable Tie Mount, 1.12 x 1.12", Use With T18-T50 Cable Tie, PA66, White, 100/pkg
Global Part Name	MB4A-PA66-WH
Length L (Imperial)	1.12
Length L (Metric)	28.5
Fixation Method	Adhesive
Width W (Imperial)	1.12
Width W (Metric)	28.5
Cable Ties	T18 - T50
Height H (Imperial)	.23
Height H (Metric)	5.8
Cable Tie Width Max (Imperial)	0.18
Cable Tie Width Max (Metric)	4.6
Mounting Hole Diameter D (Imperial)	0.18 "
Mounting Hole Diameter D (Metric)	4.6 mm
Mounting Hole Centers (Imperial)	0.8

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Adhesive	Synthetic rubber with base of polyethylene foam
Flammability	UL 94 V-2 (excluding adhesive)
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Adhesive Operating Temperature	-31°F to +158°F (-35 °C to +70 °C)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[MB4A10A2C2](#)