


## Features

- Onboard 9th Gen Intel® Xeon® E / Core™ i7/i5/i3 / Celeron® processors
- 2x DDR4 SO-DIMM sockets, Max. 32GB
- supports eDP, HDMI(2.0a) / DVI-D and DisplayPort
- 2x Intel® Gigabit LAN
- 6x USB 3.1, 4x USB 2.0, 4x COM, 4x SATA III
- 1x PCI-E (x16), 1x Mini PCI-E, 2x M.2
- Watchdog timer, Digital I/O, iAMT (11.6), TPM(2.0), iSMART, vPRO (MI996VF series)



## Specifications

CPU Socket	FCBGA1440
CPU	9th Gen Intel® Xeon® E / Core™ i7/i5/i3 / Celeron® processors
PCH	MI996VF-X28/26: Intel® CM246 PCH MI996VF-9850: Intel® QM370 PCH MI996EF-9100/ 4930: Intel® HM370 PCH
Memory	2x DDR4-2666 SO-DIMM socket, Max. 32GB (supports ECC by CPU SKUs)
BIOS	AMI
Watchdog Timer	256 levels
H/W Monitor	Yes
Storage Device Interface	mSATA, M.2
Expansion Slots	1x PCI-E (x16)
Mini Type Slots	1x Mini PCI-E 1x M.2 (M-Key, type:2280, NVMe) 1x M.2 (E-Key, type:2230, CNVi)
Graphics Controller	9th Gen Intel® Xeon®/ Core™ i7/i5/i3 processor integrated
Video Output	Supports eDP, HDMI(2.0a), DisplayPort and DVI-D
Ethernet	LAN 1: MI996VF-Series: Intel® I219LM Gigabit LAN PHY MI996EF: Intel® I219V Gigabit LAN PHY LAN 2: MI996VF-X26/28: Intel® I210AT Gigabit LAN MI996VF-9100/MI996EF-9100: Intel® I211AT or I210AT Gigabit LAN
I/O Chipset	Fintek F81964D-I
Serial Port	2x RS232/422/485, 2x RS232
USB 2.0	4x USB 2.0 via pin header
USB 3.X	6x USB 3.1 on board
Serial ATA	MI996VF-X26/28: 4x SATA III MI996VF-9850, MI996EF-9100: 2x SATA III
Audio	Intel® [CNL PCH-H integrated] built-in HD audio + Realtek ALC888S codec
TPM	TPM (2.0)
Others	Digital I/O (4-in/4-out); TPM 2.0, iSMART, EuP/ErP, RAID, iAMT (11.6), ATX
Dimensions (L x W)	170mm x 170mm (6.7" x 6.7")
Power Consumption	Intel® Xeon E-2176G, 3.7GHz w/ 8GB DDR4-2400 +12V: 7.73A, +5V: 1.59A, +5VBS: 0.17A, +3.3V: 0.32A
Operating Temperature	0°C~60°C (32°F~140°F)
Storage Temperature	-20°C~80°C (-4°F~176°F)
Relative Humidity	90% (non-condensing @60°C)

## Ordering Information

MI996VF-X28	FCBGA1440 Intel® CM246/ Xeon® E-2276ME Mini-ITX motherboard, w/ HDMI (2.0a), DisplayPort, DVI-D and eDP, dual Gigabit LAN, TPM (2.0), RAID, vPro, iAMT (11.6), iSMART (3.8), CPU cooler on board
MI996VF-9850	FCBGA1440 Intel® QM370/ Core™ i7-9850HE Mini-ITX motherboard, w/ HDMI (2.0a), DisplayPort, DVI-D and eDP, dual Gigabit LAN, TPM (2.0), RAID, vPro, iAMT (11.6), iSMART (3.8), CPU cooler on board
MI996EF-9100	FCBGA1440 Intel® HM370/ Core™ i3-9100HL Mini-ITX motherboard, w/ HDMI (2.0a), DisplayPort, DVI-D and eDP, dual Gigabit LAN, TPM (2.0), EuP/ErP, CPU cooler on board
MI996EF-4930	FCBGA1440 Intel® HM370/ Celeron® G4930E Mini-ITX motherboard, w/ HDMI (2.0a), DisplayPort, DVI-D and eDP, dual Gigabit LAN, TPM (2.0), EuP/ErP, CPU cooler on board

## Dimensions and Drawing

