

Specification Sheet

Part Number: GTM100A0C2



Adhesive with 1/4" screw hole mount secures .75" grip ties for use on flat surfaces

Grip Tie Mount for 0.75" Wide Grip Tie, Adhesive, PA66UV, Black, 100/pkg

|                     |                                                                                                                                                                                                                                                                                                              |
|---------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Article Number      | 130-91001                                                                                                                                                                                                                                                                                                    |
| Type                | GTM100A                                                                                                                                                                                                                                                                                                      |
| Color               | Black (BK)                                                                                                                                                                                                                                                                                                   |
| Quantity Per        | pack                                                                                                                                                                                                                                                                                                         |
| Product Description | To secure bundles to flat surfaces, HellermannTyton offers a mounting base to be used with the Grip Ties. Available with or without adhesive, two sizes of Grip Tie mounts cover every size of Grip Tie. The mounts are manufactured from nylon 6/6 material and are UV-stabilized for outdoor applications. |
| Short Description   | Grip Tie Mount for 0.75" Wide Grip Tie, Adhesive, PA66UV, Black, 100/pkg                                                                                                                                                                                                                                     |
| Global Part Name    | GTM100A-PA66UV-BK                                                                                                                                                                                                                                                                                            |

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| Length L (Imperial)                 | 3.25                                 |
| Length L (Metric)                   | 82.55                                |
| Fixation Method                     | Adhesive                             |
| Identification Plate Position       | none                                 |
| Releasable Closure                  | Yes                                  |
| Tie Closure                         | hook and loop                        |
| Variant                             | Grip Tie                             |
| Width W (Imperial)                  | 1.5                                  |
| Width W (Metric)                    | 38.1                                 |
| Bolt Size                           | 1/4"                                 |
| Mounting Hole Diameter D (Imperial) | 0.25                                 |
| Mounting Hole Diameter D (Metric)   | 6.35 mm                              |
| Material                            | Polyamide 6.6 UV-stabilized (PA66UV) |
| Material Shortcut                   | PA66UV                               |
| Adhesive                            | Urethane foam                        |

|                              |                                  |
|------------------------------|----------------------------------|
| UV Resistant (Yes/No)        | Yes                              |
| Use Conditions               | For Indoor and Outdoor Use       |
| Operating Temperature        | -40°F to +185°F (-40°C to +85°C) |
| Reach Compliant (Article 33) | Yes                              |
| ROHS Compliant               | Yes                              |
| Package Quantity (Imperial)  | 100                              |
| Package Quantity (Metric)    | 100                              |
| Customs Number               | 3926909988                       |

7930 N. Faulkner Road, Milwaukee, WI 53224  
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.  
[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)