REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A	Initial Release	2016/05/09	Spring	Change Rev.01 To Rev.A
B	C220629	2022/05/03	Vicky	B X4
C	C230084	2023/01/30	Vicky	C X1





Conn.

B CBD-XXAMMM-QL8FXX

XX: No. Of Pin

XX:01~99Meters
01:01Meter
02:02Meters
:
99:99Meters

B
Note:
* RoHS Compliant
* QC Important dimension
C * Waterproof rate: IP68, mated 1m/24h
* Connector
  Housing: Thermoplastic, Black
  Pin: Copper alloy, Gold plated
  Outer mold: Thermoplastic, Black
* Cable: UL21996 (26#*2P+D+AL)+16#*3C+F+AL,
  PVC Jacket, OD=11.0, Black
* Cable length tolerance: 1M: +50/-0 mm
  1M < L ≤ 3M: +100/-0 mm
  3M < L ≤ 5M: +150/-0 mm
  5M < L ≤ 10M: ±100 mm
  10M < L ≤ 20M: ±200 mm
  20M < L ≤ 30M: ±300 mm
  30M < L ≤ 99M: ±500 mm

Conn.



8P

Pin Assignments Front View

Conn.	Wire Color		Pin Out
8	Drain (26AWG)	地線	
7	Blue (26AWG)	藍	Twist 對線
6	Red (26AWG)	紅	Twist 對線
5	Green (26AWG)	綠	
4	White (26AWG)	白	
3	Black (16AWG)	黑	
2	Green (16AWG)	綠	
1	White (16AWG)	白	

UNIT: mm

TOLERANCE ±0.5mm

TITLE: XLOK, C-10A+5A, CABLE W/SR M, M, MOLDING, PUSH LOCK B

SCALE 1:1 | SIZE A4 | SHEET 1 OF 1

REV. C | WC-REV. A.1 | QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
	Spring	2016-05-09
DWG NO: B CBD-XXAMMM-QL8FXX	CHECKED BY: Fisher	DATE: 2016-05-09
CUSTOMER: ALTW	APPROVED BY: Kevin	DATE: 2016-05-09

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.