

Specification Sheet

Part Number: 151-00997

- Designed for use with MCT18 - MCT50 cable ties to provide stability when securing bundles.
- Suitable for applications with minimal space.
- Mount has 4-way entry design for use in line or at 90° angle to cable run.
- Metal content dispersed throughout mount ensures identification by metal detectors and X-ray machines.
- Industry standard blue color assists with visual detection and reduces the risk of contamination.



Metal Content Cable Tie Anchor Mount, 0.81" Hole Dia., 0.20" Max Tie Width, PA66MP+, Blue, 100/pkg

Article Number	151-00997
Type	MCCTAM1
Color	Blue (BU)
Quantity Per	pack

Product Description	The MCCTAM1 anchor mounts are for use with HellermannTyton MCT18 - MCT50 Series cable ties to provide stability when securing bundles. The Metal Content Mount is specifically designed for the food, beverage and pharmaceutical processing industries to meet the safety standards set by the Hazardous Analysis of Critical Control Point (HACCP). The mount is nylon-based with metal content dispersed throughout allowing for the part to be identified by metal detectors or X-ray inspections, reducing the risk of contamination.
Short Description	Metal Content Cable Tie Anchor Mount, 0.81" Hole Dia., 0.20" Max Tie Width, PA66MP+, Blue, 100/pkg
Global Part Name	MCCTAM1-PA66MD-BU
Length L (Imperial)	0.81
Length L (Metric)	20.7
Fixation Method	Screw Mount
Width W (Imperial)	0.41
Width W (Metric)	10.3
Cable Ties	MCT18 - MCT50
Height H (Imperial)	0.20
Height H (Metric)	5.1
Cable Tie Width Max (Imperial)	0.20
Cable Tie Width Max (Metric)	5.2

Mounting Hole Diameter D (Imperial)	0.17 "
Mounting Hole Diameter D (Metric)	4.3 mm
Mounting Hole Diameter D Max (Metric)	4.3
Material	Polyamide 6.6, metal detectable (PA66MD)
Material Shortcut	PA66MD
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)