

Specification Sheet

Part Number: 151-02457



Multiple available orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters.

Clip can be installed by hand – no need for hardware or tools.

Design provides low insertion and high extraction force, for simple, secure performance.

Clip keeps bundle away from areas that could cause damage due to rubbing.

Standoff Bundling Clip, 2.36" Long, 0.02 - 0.23" Panel Thickness, PA66HIRHSUV, Black, 5000/carton

Article Number	151-02457
----------------	-----------

Type	SOBC25FT8
------	-----------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	Tape clips are designed to provide simple and easy methods of securing cable bundles, hoses, or pipes.
---------------------	--

Short Description	Standoff Bundling Clip, 2.36" Long, 0.02 - 0.23" Panel Thickness, PA66HIRHSUV, Black, 5000/carton
-------------------	---

Global Part Name	SOBC25FT8-PA66HIRHSUV-BK
------------------	--------------------------

Length L (Imperial)	2.36
Length L (Metric)	60.0
Offset Length (Metric)	25.3
Fixation Method	Fir Tree
Width W (Imperial)	1.377
Width W (Metric)	35.0
Height H (Imperial)	0.7
Height H (Metric)	17.9
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.23
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	5.75
Mounting Hole Diameter D (Imperial)	0.30 - 0.33 "
Mounting Hole Diameter D (Metric)	7.6 - 8.4 mm M10 x 1.5
Mounting Hole Diameter D Min (Imperial)	0.30
Mounting Hole Diameter D Max (Imperial)	0.33

Mounting Hole Diameter D Max (Metric)	8.4
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	5000
Package Quantity (Metric)	5000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)