

Specification Sheet

Part Number: 151-02655

- 90 degree channel allows specific guidance around corners or obstructions.
- U-Shape channel provides three sides of protection for wire or bundle.
- High-quality polypropylene material with high heat resistance.
- Protects against abrasion and other environmental factors.
- Mounting holes for cable ties allow for easy bundling.



Mini Channel, 5.9" Long, 180° Angle, Straight, PPT20, Black, 500/pkg

Article Number	151-02655
Type	150STRTCHNL
Color	Black (BK)
Quantity Per	pack
Product Description	HellermannTyton Mini Channels provide protection and configurable routing in a cost-effective wire management solution. The variety of sizes and configurations enables engineers and installers to create optimum routing scenarios. Mini channels replace engineered channels that are costly to design and develop.
Short Description	Mini Channel, 5.9" Long, 180° Angle, Straight, PPT20, Black, 500/pkg

Global Part Name	150STRTCHNL-PPTD20-BK
------------------	-----------------------

Length L (Imperial)	5.9
---------------------	-----

Length L (Metric)	150.0
-------------------	-------

Width W (Imperial)	0.06
--------------------	------

Width W (Metric)	1.5
------------------	-----

Height H (Imperial)	0.60
---------------------	------

Height H (Metric)	15.0
-------------------	------

Mounting Hole Diameter D (Imperial)	0.24 - 0.27 "
-------------------------------------	---------------

Mounting Hole Diameter D (Metric)	6.2 - 6.8 mm
-----------------------------------	--------------

Mounting Hole Diameter D Min (Imperial)	0.24
---	------

Mounting Hole Diameter D Max (Imperial)	0.27
---	------

Mounting Hole Diameter D Max (Metric)	6.8
---------------------------------------	-----

Material	Polypropylene 20% Talkum (PPTD20)
----------	-----------------------------------

Material Shortcut	PPTD20
-------------------	--------

Flammability	UL 94 HB
--------------	----------

Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +149°F (-40°C to +65°C)
Reach Compliant (Article 33)	No
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)