

Specification Sheet

Part Number: MB2.5A10M4


For use with HellermannTyton T18 cable ties to provide stability when securing bundles.

4-way opening allows cable ties to be installed parallel or perpendicular to bundles.

The rubber-based adhesive is an economical choice ideal for indoor applications, with a static load weight of 0.3 lb.

Four predrilled holes extend mounting options and solutions.

Extended adhesive liner is easy to remove quickly.



Rubber Adhesive Cable Tie Mount, 0.63 x 0.63", Use With T18 Cable Tie, PA66, White, 1000/pkg

Article Number	151-00298
----------------	-----------

Type	MB2.5A
------	--------

Color	White (WH)
-------	------------

Quantity Per	pack
--------------	------

Product Description	Adhesive Fastened Mounting Bases are used with 18 through 150 lb. cable ties to provide stability when securing bundles. The mounts are installed using the adhesive backing and/or by securing two or four screws. The four-way opening allows the cable ties to be inserted parallel or perpendicular to the wire bundles.
---------------------	--

Short Description	Rubber Adhesive Cable Tie Mount, 0.63 x 0.63", Use With T18 Cable Tie, PA66, White, 1000/pkg
Global Part Name	MB2.5A-PA66-WH
Length L (Imperial)	0.63
Length L (Metric)	15.9
Fixation Method	Adhesive
Width W (Imperial)	0.63
Width W (Metric)	15.9
Cable Ties	T18
Height H (Imperial)	0.16
Height H (Metric)	4.1
Cable Tie Width Max (Imperial)	0.1
Cable Tie Width Max (Metric)	2.54
Mounting Hole Diameter D (Imperial)	0.11 "
Mounting Hole Diameter D (Metric)	2.8 mm

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Adhesive	Synthetic rubber with base of polyethylene foam
Flammability	UL 94 V-2 (excluding adhesive)
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Adhesive Operating Temperature	0°F to +150°F (-18 °C to +66 °C)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)