

Specification Sheet

Part Number: 151-00834

HellermannTyton Connector Clips provide a single method to mount connectors to various surfaces in a variety of applications.

Highly engineered designs feature anti-rattle discs, anti-rotation oval fir trees and clamps for mounting on edges.

An assortment of Connector Cips is available to fit the variety of connector slot designs made by most of the largest global connector manufacturers.



Connector Clip with Oval Fir Tree, 6.2x12.2mm Hole Dia, PA66HIRHS, Black, 10,000/box

Article Number 151-00834

Type YCCKSFT62x122PT1.7-2.3 90°

Color Black (BK)

Quantity Per pack

Product Description Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.

Short Description Connector Clip with Oval Fir Tree, 6.2x12.2mm Hole Dia, PA66HIRHS, Black, 10,000/box

Length L (Metric) 27.0

Fixation Method Fir Tree for oval holes

Width W (Metric) 21.0

Height H (Metric) 12.1

Panel Thickness Min (Imperial) 0.07

Panel Thickness Max (Imperial) 0.09

Panel Thickness Min (Metric) 1.7

Panel Thickness Max (Metric) 2.3

Mounting Hole Diameter D (Imperial) 0.24 x 0.48 "

Mounting Hole Diameter D (Metric) 6.2 x 12.2 mm

Mounting Hole Diameter D Min (Imperial) 0.24

Mounting Hole Diameter D Max (Imperial) 0.24

Mounting Hole Diameter D Max (Metric) 6.2

Material

Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)

Material Shortcut

PA66HIRHS

UV Resistant (Yes/No)

No

Use Conditions

For Indoor and Outdoor Use

Operating Temperature

-40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33)

Yes

ROHS Compliant

Yes

Package Quantity (Imperial)

10000

Package Quantity (Metric)

10000

Customs Number

3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)