

Specification Sheet

Part Number: 151-04073



Soft TPE over-mold prevents axial slide/rotation and protects sensitive HV cables.

Modular connector clip design eliminates the need for investment in expensive tools for TPE products or upsetting of tubes and pipes.

Compact size for mounting in tight spaces.

Fine-pitch ratchet provides controlled grip for a range of pipe sizes with one part.

Fully enclosed clamp prevents slip, crush and fallout under vacuum.

Release latch with simple twist of screwdriver.

Article Number	151-04073
Type	SGROC15.5-20SLOT17
Color	Black (BK)
Quantity Per	carton

Product Description	The Ratchet O-Clamp is designed for tight spaces, maintaining a low-profile, adjustable grip around a routing while providing a robust mounting solution. Designed for fluid routing and high-voltage cable management, this clamp includes a TPE liner to protect the routing and keep it in position. HellermannTyton's connector clips provide a single method to mount connectors to various surfaces in a variety of applications. Slot can be paired with any HellermannTyton standard USCAR17 connector clip mount.
Short Description	Soft-Grip Ratchet O-Clamp, 17mm Connector Clip Slot, 0.61 - 0.79" Bundle Dia, PA66HIRHSUV/TPE, Black, 1000/ctn
Global Part Name	SGROC15.5-20SLOT17-PA66HIRHSUV/TPE-BK
Minimum Tensile Strength (Imperial)	100
Minimum Tensile Strength (Metric)	445
Length L (Imperial)	2.29
Length L (Metric)	58.1
Fixation Method	Connector Clip
Width W (Imperial)	1.00
Width W (Metric)	25.5
Bundle Diameter Min (Imperial)	0.61
Bundle Diameter Min (Metric)	15.5
Bundle Diameter Max (Imperial)	0.79

Bundle Diameter Max (Metric)	20.0
Height H (Imperial)	1.93
Height H (Metric)	49.00
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) Thermoplastic Elastomer (TPE)
Material Shortcut	TPE PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)