REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A	Initial Release	2009/04/15	Doreen	Change REV.02 To REV.A
B	LEN147026I~4	2014/07/21	Tony_leng	Change "58.5" To "58.0".
C	C231382	2023/11/01	Ruru	C X8



UMN-000505-0MF-CSCXX

XX:01~99 Meters
01:01 Meter
02:02 Meters
:
:
99:99 Meters
Cable Length(L):01~99 Meters

Note: C
* RoHS Compliant
* QC Important dimension
* C1
  Waterproof rate: IP68, mated 1m/24h
  Housing: Thermoplastic, Black
  Pin: Copper alloy, Gold plated
  Nut: Metal
  Outer Mold: Thermoplastic, Black
* C2
  Waterproof rate: IP68, mated 1m/24h
  Housing: Thermoplastic, Black
  Pin: Copper alloy, Gold plated
  Nut: Metal
  O-Ring: Rubber, Gray
  Outer Mold: Thermoplastic, Black
* Cable: NON CERT, PVC Jacket, Gray
* Cable Length Tolerance: 01M:±40mm
  02M~05M:±60mm
  06M~10M:±100mm
  11M~30M:±200mm
  31M~99M:±500mm

C



Conn.1
Pin Assignments
Front View

C



Conn.2
Pin Assignments
Front View

Conn.2	Wire Color	Conn.1
5	Blue 藍	5
4	White 白	4
3	Black 黑	3
2	Red 紅	2
1	Drain 地線	1

Pin Out

UNIT:mm	TITLE: ACC, NMEA, APVD, DB-ENDED MF, 55 C		ITEM NO	DRAWN BY: Ruru	DATE: 2023-11-01
TOLERANCE: ±0.5 mm	SCALE: 4:5	SIZE: A4	SHEET 1 OF 1	DWG NO: UMN-000505-0MF-CSCXX	CHECKED BY: Rita	DATE: 2023-11-01
	REV.: C	WC-REV.: A.1	QC:Inspection item	CUSTOMER: ALTW	APPROVED BY: Fred	DATE: 2023-11-01

Amphenol LTW
安費諾亮泰企業股份有限公司

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.