


Specification Sheet

Part Number: 151-01884



Proprietary oval fir tree design allows this bundling clip to be used in 4 different hole sizes and various panel thicknesses without compromising performance.

Extra firm grip onto the panel is due to the branches on all four sides of the mount.

Bundling Clip with Oval Fir Tree, 1.52" L, 0.02 - 0.10" Panel Thickness, PA66HIRHS, Natural, 8000/ctn

Article Number	151-01884
Type	BCSFTOVAL2
Color	Natural (NA)
Quantity Per	carton
Product Description	Half-length tape clip with oval fir tree mount accommodates tape or cable ties to fasten bundles or cables to a surface. The oval fir tree supports a variety of hole sizes and panel thicknesses. Materials perform optimally in a wide range of environmental and temperature conditions.
Short Description	Bundling Clip with Oval Fir Tree, 1.52" L, 0.02 - 0.10" Panel Thickness, PA66HIRHS, Natural, 8000/ctn
Global Part Name	BCSFTOVAL2-PA66HIRHS-NA

Minimum Tensile Strength (Imperial)	25
Minimum Tensile Strength (Metric)	110
Length L (Imperial)	1.52
Length L (Metric)	38.7
Fixation Method	Fir Tree for oval holes
Width W (Imperial)	0.29
Width W (Metric)	7.37
Height H (Imperial)	0.46
Height H (Metric)	11.6
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.10
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	2.5
Mounting Hole Diameter D (Imperial)	0.25 x 0.50 " 0.27 x 0.47 " 0.24 x 0.48 "
Mounting Hole Diameter D (Metric)	7.0 x 12.0 mm 6.2 x 12.2 mm 6.5 x 12.5 mm 6.5 x 13.0 mm
Mounting Hole Diameter D Min (Imperial)	0.24

Mounting Hole Diameter D Max (Imperial) 0.50

Mounting Hole Diameter D Max (Metric) 13.0

Material Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)

Material Shortcut PA66HIRHS

Flammability UL 94 HB

Halogen Free Yes

UV Resistant (Yes/No) No

Use Conditions For Indoor Use Only

Operating Temperature -40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Package Quantity (Imperial) 8000

Package Quantity (Metric) 8000

Customs Number 3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)