

Specification Sheet

Part Number: 157-00292



Covers top of stud for protection from stud end.

Four-pawl, three-tooth design delivers outstanding stud retention to keep bundles secure.

PA46 material option allows use in high-heat applications.

Article Number 157-00292

Type T80ROSSB12U

Color Black (BK)

Quantity Per pack

Product Description Stud Mount Ties offer outstanding stud retention. With their low insertion force and high extraction performance, HellermannTyton mounting ties offer the ideal combination of high-grade materials and superior design to suit the mounting and bundling needs of complex applications. Available in standard and high-heat material options.

Short Description M12 Stud Mount Tie, 7.5" Tie, 80lb Tensile Strength, PA66HIRHS, Black, 2000/pkg

Global Part Name T80ROSSB12U-PA66HIRHSUV-BK

| | |
|-------------------------------------|--------------|
| Minimum Tensile Strength (Imperial) | 80 |
| Minimum Tensile Strength (Metric) | 355 |
| Length L (Imperial) | 8.6 |
| Length L (Metric) | 218.0 |
| Fixation Method | Stud Mount |
| Identification Plate Position | none |
| Releasable Closure | No |
| Tie Closure | plastic pawl |
| Width W (Imperial) | 0.93 |
| Width W (Metric) | 23.75 |
| Bundle Diameter Min (Imperial) | 0.14 |
| Bundle Diameter Min (Metric) | 3.5 |
| Bundle Diameter Max (Imperial) | 1.97 |
| Bundle Diameter Max (Metric) | 50.0 |
| Cable Ties | 157-00292 |
| Height H (Imperial) | 0.70 |

| | |
|-------------------------------------|--|
| Height H (Metric) | 17.0 |
| Mounting Hole Diameter D (Imperial) | 0.47 x 0.07 " |
| Mounting Hole Diameter D (Metric) | M12 x 1.75 |
| Stud Diameter (Metric) | 12.0 mm |
| Stud Diameter (Imperial) | 0.47 |
| Material | Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) |
| Material Shortcut | PA66HIRHSUV |
| Flammability | UL 94 HB |
| UV Resistant (Yes/No) | Yes |
| Operating Temperature | -40°F to +221°F (-40°C to +105°C) |
| Reach Compliant (Article 33) | Yes |
| ROHS Compliant | Yes |
| Package Quantity (Imperial) | 2000 |
| Package Quantity (Metric) | 2000 |

Customs Number

3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)