

Specification Sheet

Part Number: 169-60309

Tubing provides full coverage where spiral wrap or other coverings may not be suitable.

In harsh applications the tubing provides resistance to crushing, impact, and abrasion.

Tubing offers excellent protection against automotive fluids, vibration wear, water, snow, ice, and the effects of heat, cold, and sunlight on cables and wires.



Convoluted Tubing, Flame Retardant, Unslit, 0.38" Dia, PE, Gray, 1500 ft/ctn

Article Number 169-60309

Type CTPFR380UNSLIT

Color Gray (GY)

Quantity Per carton

Product Description HellermannTyton's Convoluted Tubing, also known as Loom Tubing, provides an efficient method of routing and protecting wire harness assemblies. It can also serve to protect valuable hoses and cables. Convoluted tubing offers excellent protection against vibration wear, water, snow, ice and the effects of heat, cold and sunlight on cables and wires. The polyethylene flame-retardant material provides additional protection that is suitable for applications requiring a self-extinguishing material and complies with UL 94 V2 standards.

Short Description	Convoluted Tubing, Flame Retardant, Unslit, 0.38" Dia, PE, Gray, 1500 ft/ctn
Global Part Name	CTPFR380UNSLIT-PE-FR-GY
Length L (Imperial)	1500.0
Length L (Metric)	457.2
Variant	Unslit
Bundle Diameter Min (Imperial)	0.1
Bundle Diameter Min (Metric)	1.0
Bundle Diameter Max (Imperial)	0.38
Bundle Diameter Max (Metric)	9.7
Inner Diameter D (Imperial)	0.380
Inner Diameter D (Metric)	9.65
Diameter D (Imperial)	0.526
Diameter D (Metric)	13.36
Outside Diameter OD (Imperial)	0.526
Outside Diameter OD (Metric)	13.36
Nominal Diameter (Imperial)	0.38

Nominal Diameter (Metric)	9.65
Wall Thickness WT (Imperial)	0.005
Wall Thickness WT (Metric)	0.127
Material	Polyethylene, flame retardant (PE-FR)
Material Shortcut	PE-FR
Flammability	UL 94 V-2
Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1500
Package Quantity (Metric)	457.20
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)