| Rev | AWO # | Description | Date | Appr |
|---|---|---|---|---|
| - | | RELEASED | 9/14/20 | |

APPROVED: _____

DATE: _____ TITLE: _____




| PART NUMBER | DESCRIPTION | Housing&Insert color | Cap color |
|---|---|---|---|
| OPSA1ASNC1N1 | SC/APC, W/O Panel Ground | PBT 7737C Green | PBT Black |
| OPSA1ASNC1P1 | SC/APC, W/Panel Ground | PBT 7737C Green | PBT Black |
| OPSB1ASNC1N1 | SC/PC, W/O Panel Ground | PBT 2184C Blue | PBT Black |
| OPSB1ASNC1P1 | SC/PC, W/Panel Ground | PBT 2184C Blue | PBT Black |

**SPECIFICATIONS:**

Material:

Housing: PBT, rated UL 94V−0, Color: See Chart

Cap: PBT, rated UL 94V−0, Color: Black

Sleeve: Zirconia ceramic

Electrical:

Standards of IEC, EIA/TIA, Telcordia

Repeatability: 500 min

Insertion loss: 0.2dB max

Interchangeability: 0.2dB max

Repeatability: 0.2dB max

Temperature Rating:

Operating temperature: −25°C to +85°C

Environmental:

Lead free, RoHS compliant.

RoHS COMPLIANT

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MILLIMETERS
TOLERANCES: EXCEPT AS NOTED

| MM | | ANGLE | |
|---|---|---|---|
| X. | ± 0.35 | X° | ±2° |
| .X | ± 0.30 | .X° | ±1° |
| .XX | ± 0.25 | .XX° | ±0.5° |
| .XXX | ± 0.15 | .XXX° | ±0.5° |

| APPROVALS | | DATE |
|---|---|---|
| DRAWN | OW | 9/14/20 |
| CHECKED | JL | 9/14/20 |
| APPROVED | | |


ADAM TECH INTERCONNECTS
909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710


TITLE
SC TYPE ADAPTER, APC&PC, 1 PORTS, LONG EARS, WITH SC TWO TYPE DUST CAP, SOLID BLOCK

| SIZE | PART NO. | REV. |
|---|---|---|
| X | OPSX1ASNC1X1 | - |

REF: S00005C | SCALE: NTS | SHEET 1 OF 1