Rev	AWO #	Description	Date	Appr
-		RELEASED	04/10/12	

APPROVED: _____

DATE: _____ TITLE: _____









DESCRIPTION	MATERIAL	FINISH
GASKET	RUBBER	ORANGE
RETAINING RING	SK-5	NICKEL
SPRING	SK-5	NICKEL
WASHER	IRON	NICKEL
SHELL	BRASS	NICKEL
FERRULE	BRASS	NICKEL
DIELECTRIC	TEFLON	NONE
PIN	BRASS	GOLD
BODY	BRASS	NICKEL

SPECIFICATIONS:

Frequency range: DC–4 GHz
Nominal Impedance; 50 OHMS
Working Voltage: 500 VOLTS max.
Dielectric Withstanding Voltage: 1500 VRMS min.
Temperature Rating:
Operating temperature: –65°C to +165°C
Environmental:
Lead free, RoHS compliant.

RoHS COMPLIANT

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS		DATE
DRAWN	TW	04/10/12
CHECKED	AY	04/10/12
APPROVED		

ADAM TECH
909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE: BNC CONNECTOR, 50 OHMS, RG174

SIZE	PART NO.	REV.
X	RF1-03-T-02-50	-

REF: S00011T | SCALE: NTS | SHEET 1 OF 1