

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/4/26	


APPROVED: _____

DATE: _____ TITLE: _____





SECTION A–A



SECTION B–B

SPECIFICATIONS:
Material: CuSn6, Nickel Plated
Electrical:
Current rating: 13A
Mechanical:
Crimp Specification: 0.75–2.0mm² (18–14Awg) Wire Press
Environmental:
Lead free, RoHS compliant

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	.X	± .10	HOLES	Ø.X	±.10
	.XX	± .020		Ø.XX	±.015
	.XXX	± .015		Ø.XXX	±.010

DRAWN	LH	11/4/26
CHECKED	RC	11/4/26
APPROVED		

CONFIDENTIAL AND PROPRIETARY
© Adam Tech. All rights reserved. This document contains confidential and proprietary information belonging to Adam Tech. It is provided solely for design and reference purposes by authorized parties. Any reproduction, distribution, display, or disclosure to third parties, in whole or in part, without the prior written consent of Adam Tech, is strictly prohibited. Adam Tech retains all rights, including copyright, trademark, trade secret, and all other intellectual property rights worldwide.

ADAM TECH
909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
adam-tech.com

TITLE
AUTOMOTIVE CONNECTORS FEMALE TERMINAL FOR XT SERIES, NICKEL PLATED, 18-14AWG

SIZE	PART NO.	REV.
X	SXF-CTXT-F-R	-

REF:	SCALE:	SHEET
S00238C	NTS	1 OF 1