

## Specification Sheet

Part Number: 181-00211

Strong fingers prevent unwanted breaking.

Fingers are easily deflected outward, allowing ready positioning of the wires within the slotted wall duct.

Restricted opening design in the finger of the duct helps keep wires in place.

Restricted opening prevents unintended removal of wires and permits any individual wire to be traced without disconnection.

Supplied with mounting holes to streamline installation.

Optional covers enhance protection and appearance.



Slotted Wall Wiring Duct, 1.5" x 3", Non-Adhesive, PVC, Intrinsic Blue, 60ft/Carton

Article Number 181-00211

Type SL1.5X3

Color Intrinsic Blue (IBU)

Quantity Per carton

**Product Description**

Manufactured from the same PVC material as standard Pro-Duct colors, HellermannTyton also offers an intrinsic blue color option. The intrinsic blue color indicates that the wiring contained in the duct runs to intrinsically safe components in the control panel. Pro-Duct slotted wall wiring duct features break-away fingers which provide additional access for wire leads. Each section of the duct is provided with two score lines. The upper score line is used to break away fingers when a greater opening is required. The lower score line allows the sidewall to be smoothly cut for joints and Ts.

**Short Description**

Slotted Wall Wiring Duct, 1.5" x 3", Non-Adhesive, PVC, Intrinsic Blue, 60ft/Carton

**Global Part Name**

SL1.5X3-PVC-BU

**Length L (Imperial)**

6.0

**Length L (Metric)**

1.83

**Width W (Imperial)**

1.5

**Width W (Metric)**

38.1

**Height H (Imperial)**

3.07

**Height H (Metric)**

77.90

**Mounting Hole Centers (Imperial)**

4.0

**Material**

Polyvinylchloride - rigid extrusion grade (PVC)

**Material Shortcut**

PVC

Flammability	UL 94 V-0
Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	+122°F (+50°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Certification/Specification	EN 50085-1:2005 + A1:2013 UL CSA EN 50085-2-3_1A
UL Recognized (US)	Yes
Package Quantity (Imperial)	60
Package Quantity (Metric)	18.3
Customs Number	3925900000

7930 N. Faulkner Road, Milwaukee, WI 53224  
 Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2026 HellermannTyton. All Rights Reserved.  
[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)