Product data sheet
Characteristics

ZCKE63
Limit switch head, Limit switches XC Standard, ZCKE, side metal plunger

Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch head
Device short name	ZCKE
Head type	Plunger head
Product Compatibility	XCKJ
Associated body	ZCKJ5H7 ZCKJ7H7 ZCKJD39H29 ZCKJ8 ZCKJD37H29 ZCKJ7 ZCKJD37 ZCKJ5 ZCKJD31 ZCKJ2H7 ZCKJ5H29 ZCKJ1H29 ZCKJD35H7 ZCKJ9H7 ZCKJ11H29 ZCKJ6 ZCKJD37H7 ZCKJ7H29 ZCKJD31H29 ZCKJ21H29 ZCKJ9H29 ZCKJ6H7 ZCKJD35 ZCKJ11 ZCKJ8H7 ZCKJD35H29 ZCKJ1H7 ZCKJ8H29 ZCKJ6H29 ZCKJ21H7 ZCKJD39H7 ZCKJ2 ZCKJ11H7 ZCKJ1 ZCKJ21 ZCKJ9 ZCKJ2H29 ZCKJD39 ZCKJD31H7
Movement of operating head	Linear
Type of operator	Side plunger spring return metal
Type of approach	Lateral approach, 1 direction

Complementary

Switch actuation	On end
Positive opening	With
Head material	Metal

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Ambient Air Temperature for Operation	-13…158 °F (-25…70 °C)
Ambient Air Temperature for Storage	-40…158 °F (-40…70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22411-LIMIT SWITCHES,IEC,XCKJ
Discount Schedule	T
GTIN	3389110646184
Returnability	Yes
Country of origin	ID

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.69 in (4.3 cm)
Package 1 Width	1.81 in (4.6 cm)
Package 1 Length	3.43 in (8.7 cm)
Package 1 Weight	6.28 oz (178 g)
Unit Type of Package 2	S01
Number of Units in Package 2	24
Package 2 Height	5.91 in (15 cm)
Package 2 Width	5.91 in (15 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	10.08 lb(US) (4.574 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACh Regulation	REACh Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months