


Specification Sheet

Part Number: 184-15403



Narrow fingers reduce fanning of the wires to the terminal blocks, presenting a neater appearance.

Each finger is provided with a double restriction to hold wires in the bottom portion of the duct, allowing for easier installation.

Mounting holes are uniform in size and are offered every 2 inches to accommodate compact designs and ease installation.

Optional covers snap on and off easily, and are provided with a non-slip lining that insures the covers remain in place during vibration.

High Density Slotted Wall Wiring Duct, 1.5" x 4", Non-Adhesive, PVC, White, 60ft/Carton

|                     |                                                                                                                                                                                                                                              |
|---------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Article Number      | 184-15403                                                                                                                                                                                                                                    |
| Type                | SLHD1.5X4                                                                                                                                                                                                                                    |
| Color               | White (WH)                                                                                                                                                                                                                                   |
| Quantity Per        | carton                                                                                                                                                                                                                                       |
| Product Description | HellermannTyton High-Density Slotted Wall Wiring Duct features narrow fingers equaling a 2-to-1 finger ratio compared to standard slotted wiring duct. With the narrow fingers, compact designs and components are more easily accommodated. |

|                                  |                                                                                         |
|----------------------------------|-----------------------------------------------------------------------------------------|
| Short Description                | High Density Slotted Wall Wiring Duct, 1.5" x 4", Non-Adhesive, PVC, White, 60ft/Carton |
| Global Part Name                 | SLHD1.5X4-PVC-WH                                                                        |
| Length L (Imperial)              | 6.0                                                                                     |
| Length L (Metric)                | 1.83                                                                                    |
| Fixation Method                  | Non-Adhesive                                                                            |
| Width W (Imperial)               | 1.5                                                                                     |
| Width W (Metric)                 | 38.1                                                                                    |
| Height H (Imperial)              | 4.07                                                                                    |
| Height H (Metric)                | 103.4                                                                                   |
| Mounting Hole Centers (Imperial) | 2.0                                                                                     |
| Material                         | Polyvinylchloride (PVC)                                                                 |
| Material Shortcut                | PVC                                                                                     |
| Flammability                     | UL 94 V-0                                                                               |
| Halogen Free                     | No                                                                                      |

|                              |                                                  |
|------------------------------|--------------------------------------------------|
| UV Resistant (Yes/No)        | No                                               |
| Use Conditions               | For Indoor Use Only                              |
| Operating Temperature        | +122°F (+50°C)                                   |
| Reach Compliant (Article 33) | No                                               |
| ROHS Compliant               | Yes                                              |
| Certification/Specification  | EN 50085-2-3_1A UL EN 50085-1:2005 + A1:2013 CSA |
| UL Recognized (US)           | Yes                                              |
| Package Quantity (Imperial)  | 60                                               |
| Package Quantity (Metric)    | 18.3                                             |
| Customs Number               | 3925900000                                       |

7930 N. Faulkner Road, Milwaukee, WI 53224  
 Phone: (800) 537-1512 | Email: corp@htamericas.com