

## Specification Sheet

Part Number: 318-60155

Adhesive lining provides an excellent seal against moisture and humidity.

Thin exterior wall is very flexible, while providing superior insulation of cables and components.

3 to 1 shrink ratio accommodates a wide range of component shapes and diameters.

Meets UL224 VW-1 specifications, making it ideal for high heat applications (excludes clear tubing).



Polyolefin material provides mechanical strength with good resistance to solvents, oils and fuels.

4-foot sticks are individually tagged and come in a retail box.

Heat Shrink Tubing, 4' Long Stick, Adhesive Lined, 3:1 Shrink Ratio, 3/4", 19.0/6.0 Dia, PO, Black, 15/pkg

Article Number 318-60155

Type TAN33-ST-19/6 BK

Color Black (BK)

Quantity Per pack

**Product Description**

TAN33 is a flexible, thin wall adhesive-lined heat shrink tubing with highly flame retardant properties. The 3 to 1 shrink ratio accommodates a wide range of component shapes and diameters. The adhesive lining begins to activate as the temperature reaches 176° F (80° C), to create a strong seal against moisture and humidity.

**Short Description**

Heat Shrink Tubing, 4' Long Stick, Adhesive Lined, 3:1 Shrink Ratio, 3/4", 19.0/6.0 Dia, PO, Black, 15/pkg

**Global Part Name**

TAN33-ST-19/6 BK-PO-X-BK

**Length L (Imperial)**

4.0

**Length L (Metric)**

1.22

**Variant**

Thin-Wall

**Bundle Diameter Min (Imperial)**

0.23

**Bundle Diameter Min (Metric)**

6.0

**Bundle Diameter Max (Imperial)**

0.75

**Bundle Diameter Max (Metric)**

19

**Nominal Diameter (Imperial)**

0.75

**Nominal Diameter (Metric)**

19

**Wall Thickness WT (Imperial)**

.085

**Wall Thickness WT (Metric)**

2.15

Material	Polyolefin, cross-linked (PO-X)
Material Shortcut	PO-X
Adhesive	Hot melt adhesive
Flammability	UL 224 VW-1
Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-67°F to +257°F (-55°C to +125°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	CSA
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	15
Package Quantity (Metric)	15

Customs Number

3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)