

REV. 1 8/25/98

COIL: @ 25°C

RESISTANCE	39 OHMS ± 10%
NOMINAL VOLTAGE	5.0 VDC
MUST OPERATE	2.9 VDC
MUST RELEASE	1.4 VDC MAX, 0.23 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's

SHOCK 75 g's 6 MS. DURATION

TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 2.5 MS MAX.
RELEASE TIME 4.0 MS MAX.
CONTACT BOUNCE 1.5 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 12/19/97 CK. 8/25/98

COMMUNICATIONS INSTRUMENTS, INC.

CUST. QPL
CUST. NO. M28776/6-007L

TYPE JMGAT RELAY

JMGAT-5LW