

## Specification Sheet

Part Number: 558-00006

Pre-printed header striped continuous vinyl rolls come in different header colors, providing a variety of printing options.

The headers can be printed with various ARC FLASH, WARNING And CAUTION headlines to meet OSHA safety standards for identifying electrical panels and equipment.

Signs can be designed in TagPrint Pro labeling software and printed with any HellermannTyton thermal transfer printing system with optional cutter attached.



Thermal Transfer Adhesive Labels, Solid Color Continuous Roll, 3.0 x 250', UV Stable VL, Red, 250 ft/roll

|                |           |
|----------------|-----------|
| Article Number | 558-00006 |
|----------------|-----------|

|      |          |
|------|----------|
| Type | HT3RD250 |
|------|----------|

|       |          |
|-------|----------|
| Color | Red (RD) |
|-------|----------|

|              |      |
|--------------|------|
| Quantity Per | pack |
|--------------|------|

|                     |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
|---------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product Description | Continuous Vinyl Labels are made with UV-stable materials for long outdoor life. The labels are extruded in the actual color and not colored using surface inks for long-term fade resistance. Vinyl labels are provided in continuous rolls so that the markers can be printed and cut to any length using HellermannTyton thermal transfer printing systems. Good for all surface types except powder coat painted or low surface energy substrates such as polypropylene. Test on these surfaces before approving. |
|---------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

|                           |                                                                                                           |
|---------------------------|-----------------------------------------------------------------------------------------------------------|
| Short Description         | Thermal Transfer Adhesive Labels, Solid Color Continuous Roll, 3.0 x 250', UV Stable VL, Red, 250 ft/roll |
| Global Part Name          | HT3RD250-1500-RD                                                                                          |
| Length L (Imperial)       | 250.0                                                                                                     |
| Length L (Metric)         | 76.20                                                                                                     |
| Variant                   | 3.2mil, 50lb bleached kraft paper                                                                         |
| Width W (Imperial)        | 3.0                                                                                                       |
| Width W (Metric)          | 76.2                                                                                                      |
| Thickness T (Metric)      | 64.0                                                                                                      |
| Width of Liner (Metric)   | 76.2                                                                                                      |
| Width of Liner (Imperial) | 3.0                                                                                                       |
| Material                  | Type 1500, Vinyl, UV-stabilized, glossy (1500)                                                            |
| Material Shortcut         | 1500                                                                                                      |
| Adhesive                  | Acrylic                                                                                                   |
| Halogen Free              | No                                                                                                        |

|                                |                                         |
|--------------------------------|-----------------------------------------|
| UV Resistant (Yes/No)          | Yes                                     |
| Use Conditions                 | For Indoor and Outdoor Use              |
| Adhesive Operating Temperature | -40°F to +180°F (-40°C to +82°C)        |
| Operating Temperature          | -40°F to +180°F (-40°C to +82°C)        |
| Reach Compliant (Article 33)   | Yes                                     |
| ROHS Compliant                 | Yes                                     |
| Certification/Specification    | NEC2014 NEC2011 NEC2017 NEC2020 NEC2023 |
| UL Recognized (US)             | Yes                                     |
| UL Recognized (US and Canada)  | Yes                                     |
| Package Quantity (Imperial)    | 250                                     |
| Package Quantity (Metric)      | 76.20                                   |
| Customs Number                 | 3919102055                              |
| Labels per Column              | 1                                       |
| Labels per Row                 | 1                                       |

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)