

Specification Sheet


Part Number: TAG9J-994

HellermannTyton Inkjet labels are sheet fed for easy loading and fast printing.

Inkjet labels are made with high temperature materials and adhesives so that they will not be affected by the high heat of laser printing.

Inkjet labels are printable using toner for long term UV exposure.

Inkjet labels come in a variety of label sizes and types to fit most applications.



Inkjet Label, Self-Laminating, 1.0" x .75" x 2.25", 24 Per Sheet, PET, White, 1000/pkg

Article Number 593-09994

Type TAG9J

Color White (WH)

Quantity Per pack

Product Description Ink Jet labels are durable, ink jet printable markers for applications requiring clear, crisp legibility. The labels are supplied on sheets and are printable using HellermannTyton Tagprint Pro software and a standard ink jet printer. Specially designed adhesives and topcoats accept the ink allowing for easy color printing for specific applications that require colors.

Short Description Inkjet Label, Self-Laminating, 1.0" x .75" x 2.25", 24 Per Sheet, PET, White, 1000/pkg

Global Part Name	TAG9J-994-WH
Width W (Imperial)	1.0
Width W (Metric)	25.4
Bundle Diameter Min (Imperial)	0.25
Bundle Diameter Min (Metric)	6.35
Bundle Diameter Max (Imperial)	0.47
Bundle Diameter Max (Metric)	11.94
Thickness T (Metric)	35.0
Width of Liner (Metric)	215.00
Width of Liner (Imperial)	8.5
Outside Diameter Max (Imperial)	0.45
Outside Diameter Min (Metric)	5.8
Outside Diameter Min (Imperial)	0.22
Outside Diameter Max (Metric)	11.60
Material	Type 994, Polyethylene Terephthalate (994)

Material Shortcut	994
Adhesive	Acrylic
Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Adhesive Operating Temperature	-40°F to +176°F (-40°C to +80°C)
Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3919905060
Labels per Column	3
Labels per Row	8

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)