

Specification Sheet

Part Number: 596-00474

Made with UV-stable inks and materials for durability and weather resistance.

Reflective properties to meet applicable NEC code requirements for reflective identification.

Supplied with an aggressive adhesive to ensure long life.

PHOTOVOLTAIC SYSTEM
EQUIPPED WITH
RAPID SHUTDOWN

Meets NEC & IFC standards for printed text, character height, color and outdoor UV stability to pass inspections.

Solar Label, Reflective, PHOTOVOLTAIC SYSTEM...RAPID SHUTDOWN, 5.5" x 1.75", VL, Red, 50/roll

Article Number	596-00474
Type	PSEWRS
Color	Red (RD)
Quantity Per	pack
Product Description	HellermannTyton Pre-Printed Solar Installation Labels are designed to meet the requirements of the National Electrical Code® (NEC®) and the International Fire Code (IFC) as well as being acceptable to the Authority Having Jurisdiction (AHJ). Labels are made with durable UV-stable materials and adhesives that are designed to stick to both baked enamel and powder-coated surfaces. Where applicable, labels are made using reflective materials for first responder safety. Some pre-printed labels are printable using a thermal transfer printer when variable voltage or series data must be printed and displayed.

Short Description	Solar Label, Reflective, PHOTOVOLTAIC SYSTEM...RAPID SHUTDOWN, 5.5" x 1.75", VL, Red, 50/roll
Global Part Name	PSEWRS-505/281-RD
Local Order Number 2	Cross Reference = 10 per pack: 596-00677; Spanish version 50 per roll: 596-00823
Width W (Imperial)	5.5
Width W (Metric)	139.7
Thickness T (Imperial)	0.0025
Thickness T (Metric)	64.0
Height H (Imperial)	1.75
Height H (Metric)	44.45
Material	Type 505/281, UV stabilized, reflective vinyl with clear polyester laminate (505/281)
Material Shortcut	505/281
Adhesive	Acrylic
Halogen Free	No
UV Resistant (Yes/No)	Yes

Use Conditions	For Indoor and Outdoor Use
Adhesive Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Operating Temperature	-40°F to +174°F (-40°C to +79°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	IFC 2012 UL 969 NEC2014 ANSI Standard Z535.4
Warranty (US)	Yes
UL Recognized (US)	Yes
Package Quantity (Imperial)	50
Package Quantity (Metric)	50
Customs Number	3919102055
Labels per Column	1
Labels per Row	1

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com