

Specification Sheet

Part Number: 596-01904

Flexible, tear- and impact-resistant material is suitable for marking wires and cables in harsh environments.

Polyester material delivers excellent resistance to alcohol, gasoline, cleaning agents and hydraulic oils.

High temperature and UV resistance is ideal for outdoor applications.

Laminating feature enhances protection against humidity and mechanical abrasion.

Rounded edge design resists peeling, extends longevity.



Hydraulic Label, Self-laminating, Thermal Transfer, 1.2" x 5.3", White, Polyester, 650/Roll

Article Number	596-01904
Type	TAG32-135TD1
Color	White (WH) Clear (CL)
Quantity Per	pack
Product Description	These self-laminating labels are ideal for marking hoses and pipes in harsh environments. The labels consist of a white printable area with a protective laminate to ensure the printed text is shielded from negative environmental influences such as humidity, debris and mechanical abrasion.

Short Description	Hydraulic Label, Self-laminating, Thermal Transfer, 1.2" x 5.3", White, Polyester, 650/Roll
Global Part Name	TAG32-135TD1-1232-CL/WH
Fixation Method	Pasting / Stick
Variant	Roller form
Width W (Imperial)	1.25
Width W (Metric)	31.75
Bundle Diameter Min (Imperial)	0.55
Bundle Diameter Min (Metric)	14.01
Bundle Diameter Max (Imperial)	1.22
Bundle Diameter Max (Metric)	30.88
Height H (Imperial)	1.57
Height H (Metric)	39.87
Width of Liner (Metric)	38.00
Width of Liner (Imperial)	1.49

Material	Type 1232, Polyester, Self Laminating, White Transparent (1232)
Material Shortcut	1232
Adhesive	Acrylic
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor Use Only
Adhesive Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	650
Package Quantity (Metric)	650
Customs Number	3919102055
Labels per Column	1
Labels per Row	1

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)