

Specification Sheet

Part Number: 596-00204

Pre-printed solar labels are made with UV-stable inks and materials for durability and weather resistance.

Polyester is resistant to chemicals and solvents and will remain legible in dirty environments.

NOTICE

High abrasion and scuff resistance for high performance labeling.

Meets NEC & IFC standards for printed text, character height, color and outdoor UV stability to pass inspections.

Pre-Printed Header Label, NOTICE, 6.0" x 4.0", PET, Blue, 250/roll

Article Number 596-00204

Type 4X6NOTICE

Color Blue (BU)

Quantity Per pack

Product Description

HellermannTyton Pre-Printed Solar Installation Labels are designed to meet the requirements of the National Electrical Code and the International Fire Code as well as being acceptable to the Authority Having Jurisdiction (AHJ). Labels are made with durable UV stable materials and adhesives that are designed to stick to both baked enamel and powder coat surfaces. Where applicable, labels are made using reflective materials for first responder safety. Some pre-printed labels are printable using a thermal transfer printer when variable voltage or series data must be printed and displayed.

Short Description

Pre-Printed Header Label, NOTICE, 6.0" x 4.0", PET, Blue, 250/roll

Global Part Name

4X6NOTICE-336/926-BU

Width W (Imperial)

6.0

Width W (Metric)

152.4

Thickness T (Metric)

64.0

Height H (Imperial)

4.0

Height H (Metric)

101.6

Width of Liner (Metric)

106.6

Width of Liner (Imperial)

4.2

Material

Type 336/926, Polyester, UV stabilized, clear polyester laminate (336/926)

Material Shortcut

336/926

| | |
|--------------------------------|-----------------------------------|
| Adhesive | Acrylic |
| Halogen Free | No |
| UV Resistant (Yes/No) | Yes |
| Use Conditions | For Indoor and Outdoor Use |
| Adhesive Operating Temperature | -40°F to +302°F (-40°C to +150°C) |
| Operating Temperature | -40°F to +302°F (-40°C to +150°C) |
| Reach Compliant (Article 33) | Yes |
| ROHS Compliant | Yes |
| Certification/Specification | NEC2020 NEC2014 NEC2017 NEC2011 |
| UL Recognized (US) | Yes |
| Package Quantity (Imperial) | 250 |
| Package Quantity (Metric) | 250 |
| Customs Number | 3919102055 |
| Labels per Column | 1 |
| Labels per Row | 1 |

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)