

Specification Sheet

Part Number: 596-00206

Made with UV-stable inks and materials for durability and weather resistance.

Reflective properties to meet applicable NEC code requirements for reflective identification.

Supplied with an aggressive adhesive to ensure long life.

Meets NEC & IFC standards for printed text, character height, color and outdoor UV stability to pass inspections.

WARNING: PHOTOVOLTAIC POWER SOURCE

Solar Label, Reflective, Warning Photovoltaic Power Source, 6.5" x 1.0", VL, Red, 50/roll

Article Number 596-00206

Type PVPSR

Color Red (RD)

Quantity Per pack

Product Description HellermannTyton Pre-Printed Solar Installation Labels are designed to meet the requirements of the National Electrical Code® (NEC®) and the International Fire Code (IFC) as well as being acceptable to the Authority Having Jurisdiction (AHJ). Labels are made with durable UV-stable materials and adhesives that are designed to stick to both baked enamel and powder-coated surfaces. Where applicable, labels are made using reflective materials for first responder safety. Some pre-printed labels are printable using a thermal transfer printer when variable voltage or series data must be printed and displayed.

Short Description	Solar Label, Reflective, Warning Photovoltaic Power Source, 6.5" x 1.0", VL, Red, 50/roll
Global Part Name	PVPSR-505/281-RD
Local Order Number 2	Cross Reference = 10 per pack: 596-00676
Width W (Imperial)	6.5
Width W (Metric)	165.1
Thickness T (Imperial)	0.0025
Thickness T (Metric)	64.0
Height H (Imperial)	1.0
Height H (Metric)	25.40
Width of Liner (Metric)	28.57
Width of Liner (Imperial)	1.125
Material	Type 505/281, UV stabilized, reflective vinyl with clear polyester laminate (505/281)
Material Shortcut	505/281
Adhesive	Acrylic

Halogen Free	No
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Adhesive Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Operating Temperature	-40°F to +174°F (-40°C to +79°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	NEC2017 NEC2014 UL 969 IFC 2012 NEC2011
Warranty (US)	Yes
UL Recognized (US)	Yes
Package Quantity (Imperial)	50
Package Quantity (Metric)	50
Customs Number	3919102055
Labels per Column	1
Labels per Row	1

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)