

Specification Sheet

Part Number: TAG2L-105

Laser printable self-laminating polyester has a smooth surface, allowing for the highest resolution and print contrast.

The material is 1.0 mil thick, allowing it to conform around wires and cable.

The acrylic-based adhesive bonds to a wide variety of substrates and can withstand high temperatures long term.

Lasertags are not affected by the high heat required in a laser printer.



Laser Tag Label, Self-Laminating, 0.50" x .50" x 1.43", 112 Per Sheet, PET, White, 5000/pkg

|                     |                                                                                                                                                                                                                                                                                                                                                                       |
|---------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Article Number      | 594-02105                                                                                                                                                                                                                                                                                                                                                             |
| Type                | TAG2L                                                                                                                                                                                                                                                                                                                                                                 |
| Color               | White (WH)                                                                                                                                                                                                                                                                                                                                                            |
| Quantity Per        | pack                                                                                                                                                                                                                                                                                                                                                                  |
| Product Description | HellermannTyton’s self-laminating labels are used for marking wires and cable. The clear tail overlaps and protects the printed information from abrasion, chemicals and solvents and resists UV exposure. When printed using a laser printer, clear marking and high high-contrast imaging against the wire make this the perfect choice for durable identification. |

|                                 |                                                                                             |
|---------------------------------|---------------------------------------------------------------------------------------------|
| Short Description               | Laser Tag Label, Self-Laminating, 0.50" x .50" x 1.43", 112 Per Sheet, PET, White, 5000/pkg |
| Global Part Name                | TAG2L-105-WH                                                                                |
| Width W (Imperial)              | 0.5                                                                                         |
| Width W (Metric)                | 12.7                                                                                        |
| Bundle Diameter Min (Imperial)  | 0.15                                                                                        |
| Bundle Diameter Min (Metric)    | 3.80                                                                                        |
| Bundle Diameter Max (Imperial)  | 0.29                                                                                        |
| Bundle Diameter Max (Metric)    | 7.37                                                                                        |
| Thickness T (Metric)            | 35.0                                                                                        |
| Width of Liner (Metric)         | 215.00                                                                                      |
| Width of Liner (Imperial)       | 8.5                                                                                         |
| Outside Diameter Max (Imperial) | 0.149                                                                                       |
| Outside Diameter Min (Metric)   | 3.8                                                                                         |
| Outside Diameter Min (Imperial) | 0.29                                                                                        |
| Outside Diameter Max (Metric)   | 7.60                                                                                        |

|                                |                                   |
|--------------------------------|-----------------------------------|
| Material                       | Type 105, Polyester, white (105)  |
| Material Shortcut              | 105                               |
| Adhesive                       | Acrylic                           |
| Halogen Free                   | No                                |
| UV Resistant (Yes/No)          | No                                |
| Use Conditions                 | For Indoor Use Only               |
| Adhesive Operating Temperature | -40°F to +302°F (-40°C to +150°C) |
| Operating Temperature          | -40°F to +300°F (-40°C to +149°C) |
| Reach Compliant (Article 33)   | Yes                               |
| ROHS Compliant                 | Yes                               |
| Package Quantity (Imperial)    | 5000                              |
| Package Quantity (Metric)      | 5000                              |
| Customs Number                 | 3919905060                        |
| Labels per Column              | 7                                 |
| Labels per Row                 | 16                                |

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)